


## DataShield In-Line Surge Protector for Network and Phone Lines, 2-Line RJ11/RJ45

MODEL NUMBER: DTEL2



### Highlights

- RJ11/RJ45 2-line dial-up surge protector
- Protects against the effects of electrostatic discharge, faulty wiring and lightning

### Package Includes

- DTEL2 dataline protector
- 5-in. RJ11 telephone patch cable
- Warranty information and instruction manual

Your network/phone line is vulnerable to surges and power problems. These connections provide one more entry-way for transient surges to damage your equipment. Seal off your equipment from potential damage by stopping transient surges with the DataShield™ DTEL2 Network Surge Suppressor. It protects up to 2 network or phone lines, modems, fax machines and answering machines against damage from lightning, electrostatic discharge and ground surges.

### Description

Tripp Lite's DTEL2 surge suppressor is designed to protect data and communications equipment against AC transients caused by lightning, electrostatic discharge and ground surges that can enter equipment from the signal lines or chassis ground. The DTEL2 features RJ45/RJ11 plugs for modems, telephone lines and answering or fax machines.

### Features

- Protects against the effects of electrostatic discharge, faulty wiring and lightning
- Comes with RJ11 telephone patch cable

## Specifications

OVERVIEW	
UPC Code	037332010865
OUTPUT	
Output Receptacles	(1) Network
Circuit Breaker (amps)	250
Right-Angle Outlets	No



<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Recommended Electrical Service	120V, 230V
Input Plug Type	RJ11; RJ45
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	No
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	0
Clamping Voltage (RMS)	260
Auto Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Additional Dataline Protection	4,5 & 3,6 pairs
<b>PHYSICAL</b>	
Anti-Microbial Protected	No
Color	Beige
Integrated Keyhole Mounting Slots	No
Shipping Dimensions (hwd / cm)	13.21 x 7.62 x 5.33
Shipping Dimensions (hwd / in.)	5.20 x 3.00 x 2.10
Shipping Weight (kg)	0.09
Shipping Weight (lbs.)	0.20
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>