

Keystone 86mm X 86mm Faceplate Kit

specifications

The 86mm X 86mm faceplate kit shall include a faceplate bezel and two 25mm X 50mm sloped inserts with spring shuttered doors. Each insert shall include a label pocket with a hinged label cover and label to ensure proper identification. Faceplate shall accept up to two standard Keystone modules. Faceplate shall be available in white and shall include two mounting screws.



technical information

Mounting options:	Faceplate bezel employs two mounting screw holes. Two 25mm X 50mm inserts easily snap into the faceplate bezel.
Number of ports:	2-port configuration
Packaging:	Includes 86mm X 86mm faceplate bezel, (2) 25mm X 50mm sloped, shuttered inserts, labels, and (2) m3.5 X 25mm mounting screws.
Material:	Bezel and adapter are made of ABS material

key features and benefits

Modular	Keystone Modules snap in and out for easy moves, adds and changes
Sloped ports	45° ports facilitate cable flow and provide more cable room
Spring-loaded shutter	Keeps jacks protected from dust and debris when not in use.
Labeling capability	Includes label pocket that allow ports to be properly identified

applications

Panduit Keystone Faceplates offer an aesthetic solution that complements work areas, while offering various features that enhance functionality by offering modularity and flexibility. Will support copper, fiber and audio/video applications.

As part of a global workstation outlet solution offered by Panduit. Each 25mm X 50mm insert features spring-shuttered doors that remain closed when connections are not in use to protect them from dust and debris. Built-in label pocket enable easier identification for lower cost maintenance.


86mm x 86mm Faceplates

White: KFPL88S2SWH

Keystone Shielded Jack Modules

Jack Module: KJS6X88TC

Keystone 86mm x 86mm Faceplate Kits



Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT[™]

© 2018 Panduit Corp.
ALL RIGHTS RESERVED.
NKSP63--WW-UKE
10/2018