




Max Load 25b (11.3kg)

In-Wall Accessory Box with 125V Duplex Power Receptacle

FOR RECESSED CABLE MANAGEMENT AND POWER STORAGE

Peerless-AV's In-Wall Accessory Box with 125V Duplex Power Receptacle allows cables and cords to become virtually invisible. When combined with a Peerless-AV® wall mount, the In-Wall Accessory Box provides the perfect behind-the-screen solution to conceal unsightly power and low voltage cables, like HDMI or RCA, behind flat panel displays, audio components or other devices. Complete with a receptacle knock-out for adding included duplex power module, the IBA2AC creates a professional look in any setting.



Please visit peerless-av.com/en-us/patents for patent information.

🔀 info@peerless-av.com





Model Numbers

IBA2AC(-W)

WARRANTY: Limited 5-years

AC(-W) In-Wall Accessory Box with 125V Duplex Power Receptacle for Recessed Cable Management and Power Storage

Product Specifications

	DIMENSIONS (W X H X D)	PRODUCT WEIGHT	LOAD CAPACITY	FINISH	AVAILABLE COLORS	
IBA2AC(-W)	Usable Space: 13.10" x 9.60" x 3.76" (333 x 244 x 96mm) Overall Dimensions: 17.42" x 11.00" x 3.76" (442 x 279 x 96mm)	6.5lb (2.94kg)	25lb (11.33kg)	Scratch Resistant Fused Epoxy	IBA2AC: Gloss Black IBA2AC-W: White	

Package Specifications

	PACKAGE SIZE (W x H x D)	PACKAGE SHIP WEIGHT	PACKAGE UPC CODE	PACKAGE CONTENTS	UNITS IN PACKAGE
IBA2AC(-W)	20.50" x 12.50" x 4.50" (520 x 317 x 114mm)	7lb (3.17kg)	IBA2AC: 735029275817 IBA2AC-W: 735029275831	Recessed Storage Accessory Box, Leviton Smart Grid® Tamper Resistant Duplex Receptacle, Galvanized Outlet Box with Knock Outs, Mounting Hardware, Cable Management Ties and Grommet	1


NOTES:

DO NOT run or pull the TV cord or other electrical cords inside the drywall. National Electrical Code (NEC) DOES NOT ALLOW the installation of the TV power cord or an extension cord behind the wall. When adding a duplex receptacle power outlet ONLY LICENSED PROFESSIONALS SHOULD INSTALL THIS PRODUCT. Be sure to install the Recessed Cable Management and Power Storage Accessory Box in accordance with the National Electrical Code (NEC) and local codes.

Accessories ACC415: Metal Stud Fasteners

Leviton Smart Grid® Model# T5280-E (black) & T5280-W (white) Specifications:

Joules Rating – 720 Dielectric Voltage – Withstands 2000V per UL498 Max Surge Current – L-N: 18kA, L-G: 9kA, N-G: 9kA SCCR – 5000A MCOV – 150V rms Alarm Indicator – LED Light For further information see website www.leviton.com



Architect Specifications

The In-Wall Accessory Box with 125V Duplex Power Receptacle shall be a Peerless-AV model IBA2AC(-W) shall be located where indicated on the plans. Assembly and installation shall be done according to instructions provided by the manufacturer.

Visit **peerless-av.com** to see the complete line of AV solutions from Peerless-AV, including outdoor displays, wireless, kiosks, digital audio, display mounts, projector mounts, carts/stands, and a full assortment of accessories.

Peerless-AV

2300 White Oak Circle Aurora, IL 60502 USA (800) 865-2112 (630) 375-5100 Fax: (800) 359-6500

Peerless-AV EMEA Unit 3 Watford Interchange Colonial Way, Watford

Colonial Way, Watford Herts, WD24 4WP United Kingdom +44 (0) 1923 200100 Fax: +44 (0) 1923 200101 Peerless-AV Latin America Ave de las Industrias 413 Parque Industrial Escobedo Escobedo, N.L., Mexico 66062 +52 (81) 8384-8300 Fax: +52 (81) 8384-8360

