

1/4" DRIVE EXTENSIONS AND ACCESSORIES

High-Polished Chrome Finish

Product Code	Description	Length (Inches)	
30002	Extension	1 1/2	
30003	Extension	3	
30004	Extension	6	
30007	Universal Joint Extension	1 3/8	
30009	Adaptor, 1/4" F x 3/8" M	1	
30010	Spinner Disk		
30013	Holder for 1/4" Hex Screwdriver Bits	3/4	
30023	Locking Extension	4	
30024	Locking Extension	6	
30025	Locking Extension	10	
30026	Locking Extension	12	
30027	Locking Extension	18	
30028	Locking Extension	24	

Fed. Spec: ANSI B107.10M

Features

- Chrome plating provides increased protection from rust and corrosion.
- · Ball and spring socket retention.



30013







30010

WILLIAMS

6 PIECE 1/4" DRIVE RATCHET AND DRIVE TOOL SET

Furnished in a Pouch

Product Code	Description
30920	6 Piece ¹ /4" Drive Ratchet and Accessory Set

Contents Include:

Product Code	Description	Product Code	Description
30001	36 Tooth Quick-Release Ratchet	30005	Flex Handle
30002	1 1/2" Extension	30006A	Spinner Handle
30004	6" Extension	30007	Universal Joint

Features

· All tools are professional quality, made of high-grade chrome vanadium steel.













1/4" DRIVE SHALLOW 12 POINT SOCKETS, SAE

High-Polished Chrome Finish

		Α	В	С	D	Ε		F
Product Code	Size (Inches)	OAL (Inches)	Drive End Diameter (Inches)	Working End Diameter (Inches)	Broach Depth (Inches)	Bolt Clearance Depth (Inches)	Bolt Clearance Diameter (Inches)	Nose Length (Inches)
M-1208	1/4	7/8	15/32	3/8	7/32	17/32	7/32	7/16
M-1210	5/16	7/8	15/32	15/32	9/32	17/32	7/32	-
M-1211	11/32	7/8	1/2	1/2	9/32	17/32	11/32	
M-1212	3/8	7/8	17/32	17/32	9/32	17/32	3/8	-
M-1214	7/16	7/8	19/32	19/32	3/8	17/32	7/16	
M-1216	1/2	7/8	11/16	11/16	3/8	17/32	1/2	
M-1218	9/16	29/32	3/4	3/4	3/8	17/32	7/32	

Fed. Spec: ANSI B107.110



WSM-7RC 7 Piece 1/4" Drive Shallow 12-Point Socket Set on Clip Rail

Contents Include:

Product Code	Size (Inches)						
M-1208	1/4	M-1211	11/32	M-1214	7/16	M-1218	9/16
M-1210	5/16	M-1212	3/6	M-1216	1/2		

Features

- SUPERTORQUE® lobular openings for greater turning power without deforming the fastener.
- Designed for quick engagement on both 6 and 12 point fasteners.











