

Standard LC Duplex MM / Standard LC Duplex MM, OM3 50um, 2F, Zipcord Riser, Standard Aqua Jacket 17 Meters

CORNING

Part Number: 050502T5120017M

Cable assemblies are an often overlooked, critical component of your inside plant connectivity portfolio. These products are the component that enables port replication and the ability to cost effectively transmit and receive services between the active electronics and end users. As the industry's leading supplier of cable assemblies, Corning's state-of-the-art manufacturing process ensures reliable connector performance with products that meet or exceed all industry standards for reflectance and insertion loss. Our ability to scale to meet your deployment needs is what sets us apart, along with the highest-quality fiber and factory-tested connectors. All assemblies undergo rigorous performance testing to ensure optimal quality in every connector. Constant process improvements offer a variety of options in fiber, cable, and connector types to meet your network's ever-evolving needs.

If you do not see what you are looking for here, please review the ordering matrix contained in the family specification sheet, or contact Customer Care at 1-800-743-2675.



Features and Benefits

State-of-the-art manufacturing processes

Advanced technology results in unsurpassed product consistency and quality

Global operations

Mitigates trade barriers or supply disruptions

Flexible design options

Choice of materials for strength elements and fiber properties for various application requirements

Superior performance testing

Each termination is tested to ensure the highest network performance

Standard LC Duplex MM / Standard LC Duplex MM, OM3 50um, 2F, Zipcord Riser, Standard Aqua Jacket 17 Meters

CORNING

Specifications

General Settings

Unit of Measure	Meters
-----------------	--------

Product Category	2 Fiber
------------------	---------

Furcation A

Outer Diameter	2.0mm
----------------	-------

Connector A

Connector	LC PC Dup
-----------	-----------

Connector Pairing	Duplex
-------------------	--------

Connector Keying	Non-Keyed
------------------	-----------

Color	Standard
-------	----------

Furcation B

Outer Diameter	2.0mm
----------------	-------

Connector B

Connector	LC PC Dup
-----------	-----------

Connector Pairing	Duplex
-------------------	--------

Connector Keying	Non-Keyed
------------------	-----------

Color	Standard
-------	----------

Standard LC Duplex MM / Standard LC Duplex MM, OM3 50um, 2F, Zipcord Riser, Standard Aqua Jacket 17 Meters

CORNING

Cable

Fiber Type	OM3 MM
------------	--------

Flame Rating	Riser
--------------	-------

Color	Aqua
-------	------

Length	17
--------	----

Unit of Measure	Meters
-----------------	--------

Cable Type	Zipcord
------------	---------

Fiber Mode	Multimode
------------	-----------



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2020 Corning Optical Communications. All rights reserved.