

4-Port USB Hub - USB 3.1 Gen 2, 10 Gbps, 4 USB-A Ports, Thunderbolt 3, Aluminum Housing

MODEL NUMBER: U460-004-4A-G2



USB 3.1 Gen 2 portable hub adds 4 USB-A ports to the USB-C or Thunderbolt 3 port on your MacBook, Chromebook, PC, tablet or smartphone.

Features

USB-C 3.1 Hub Connects 4 USB Peripherals to Your MacBook or Chromebook

This USB-C hub allows you to connect up to four USB peripherals to your tablet, laptop, notebook, MacBook, Chromebook, smartphone or PC. You can expand the potential of your device by connecting USB peripherals that can help you do your job faster, easier and better, such as an external hard drive, keyboard/mouse, power meter and printer.

Transfers Data at Lightning-Fast USB 3.1 Gen 2 Speeds

All four USB ports transfer data at speeds up to 10 Gbps, which is double the speed of USB 3.1 Gen 1. The USB ports are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices.

Built-In USB-C Cable Connects in Either Direction

Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package

The plug-and-play USB Type-C hub is specifically designed for use with the MacBook, Google Chromebook Pixel and other laptops, tablets and devices equipped with a USB-C or Thunderbolt 3 port. It requires no software, drivers or external power. The lightweight aluminum case fits easily into a pocket, briefcase or laptop bag for connecting on the go.

Highlights

- USB-C 3.1 Type-C hub is compatible with all USB-C and Thunderbolt 3 devices
- Accepts up to 4 USB peripherals, turning your laptop into a mini workstation
- Supports USB 3.1 Gen 2 speeds up to 10 Gbps to ensure lightning-fast data transfers
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect up to 4 USB peripherals, such as an external hard drive, MP3 player, power meter and printer
- Transfer files quickly to and from a USB thumb drive
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone
- Download photos from a digital camera

System Requirements

- Source device with USB-C or Thunderbolt 3 port (USB 3.1 Gen 2 capability required for 10 Gbps speeds)

Package Includes



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- U460-004-4A-G2 USB 3.1 C
Hub, 10 Gbps, Aluminum
Housing

Specifications

OVERVIEW	
UPC Code	037332218247
INPUT	
Built-In Cable Length (ft.)	0.492
Built-In Cable Length (m)	0.15
Built-In Cable Length (in.)	5.91
Built-In Cable Length (cm)	15
Bus Powered	Yes
BATTERY	
Battery Charging (1.2 Port)	No
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Transmitting Data (Blue)
PHYSICAL	
Cable Outer Diameter (OD)	4.0 +/- 0.15 mm
Color	Black
Material of Construction	PVC, Aluminum
Unit Dimensions (hwd / cm)	0.95 x 3.97 x 6.01
Unit Dimensions (hwd / in.)	0.37 x 1.56 x 2.37
Unit Packaging Type	Box
Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.0926
ENVIRONMENTAL	
Operating Temperature Range	32 ~ 140F (0 ~ 60C)
Storage Temperature Range	-4 ~ 140F (-20 ~ 60C)
Relative Humidity	0 ~ 90% RH (Non Condensing)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

CONNECTIONS	
Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB A (FEMALE)
Side B - Connector 2	USB A (FEMALE)
Side B - Connector 3	USB A (FEMALE)
Side B - Connector 4	USB A (FEMALE)
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)
Driver Required	No
USB Power Delivery (PD) Charging Support	No
Technology	USB 3.1 (Gen 2)
CERTIFICATIONS	
Certifications	Tested to RoHS, REACH, FCC, CE
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>