

WorkWise Wall-Mounted Workstation, Single Display

MODEL NUMBER: **WWSS1332W**



Wall-mounted workstation transforms your desk space into an ergonomic sit-stand area without modifying the work surface.

Features

Enjoy the Benefits of Standing During Your Workday

This WorkWise™ sit-stand workstation mounts to the wall using the included hardware, allowing you to enjoy the benefits of better workplace ergonomics. Standing for part of the day can help increase metabolism, improve alertness and productivity, reduce fatigue and decrease the risk of repetitive stress injuries. Ideal for home, school or office use, the WWSS1332W lets you sit or stand with 19.5 inches of single-motion height extension.

Easy to Adjust to Your Liking With a Single Touch

Just one touch is all it takes to adjust your wall-mounted workstation's angles and heights to fit your comfort level. All sections move together for smooth transitions between sitting and standing modes. The full-motion arm swivels from -90° to +90° to give you plenty of flexibility in minimizing glare and providing comfortable viewing. It also rotates 360 degrees for viewing in portrait or landscape orientation. Increase or decrease tension using the included hex key to compensate for heavier or lighter loads.

VESA-Compliant Mount Supports Up to 17.6 lb.

The VESA-compliant single-arm mount fits most flat-panel monitors, televisions and other displays from 13 to 32 inches. It's compatible with 75 x 75 mm, 75 x 100 mm, 100 x 75 mm and 100 x 100 mm VESA mounting-hole patterns.

Extra-Large Keyboard Tray Holds the Most Popular Models

The large keyboard tray, with soft padded wrist rest, measures 26.2 x 10.2 inches and flips up to save space when not in use. A secondary surface is ideal for telephones, fans and other desk accessories.

5-Year Warranty and Environmentally Responsible Design

The WWSS1332W sit-stand workstation comes with a 5-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Highlights

- Mounts firmly to wall to leave valuable desk or table space clear
- Adjusts to fit wide range of flat-screen monitors from 13 to 32 in.
- Keyboard tray with padded wrist rest flips up when not in use to conserve workspace
- Monitor swivels from -90° to +90° and rotates 360° to customize the ideal viewing angle
- Includes necessary mounting hardware so you can start installation immediately

Applications

- Transform your work area into a sit-stand environment to reap the health benefits of standing for part of your workday

Package Includes

- Bracket arm
- Support mast
- Keyboard shelf
- (2) Decorative covers
- Hex key, 4 mm
- Hex key, 6 mm
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332212740



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
Degrees of Motion	180 swivel and 360 rotate
Material of Construction	Steel and plastic
Maximum Screen Size (cm)	81.28
Maximum Screen Size (in.)	32
Maximum Weight Capacity (kg)	8
Maximum Weight Capacity (lbs.)	17.6
Minimum Screen Size (cm)	33.02
Minimum Screen Size (in.)	13
Motion	Full Motion/Rotate
Number of Displays	1
Unit Dimensions (hwd / in.)	26.2 x 31.1 x 37.6
Unit Weight (kg)	9.03
Unit Weight (lbs.)	19.9
VESA Pattern (mm)	100x100; 100x75; 75x100; 75x75
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	No
CERTIFICATIONS	
Approvals	RoHS3, REACH and CE
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>