


Butt-Splice Kit for Straight and 90-Degree Ladder Runway Sections - Hardware Included

MODEL NUMBER: SRLBUTTSPLICE



Easy-to-use butt-splice kit safely and securely connects 2 sections of cable management ladder end-to-end.

Features

Convenient Cable Ladder Connector Lengthens the Runway System in Your Data Center This SmartRack butt-splice kit creates a secure connection point between two sections of cable ladder to extend the cable runway system in your server room or data center. All mounting and installation hardware is included. The splice plates fit solid and tubular steel runway measuring 1.5 x 0.375 inches (38 x 9.5 millimeters). The SRLBUTTSPLICE is designed to connect Tripp Lite's SRCABLELADDER, SRCABLELADDER18, SRL90BEND12, SRL90BEND18 and other compatible straight and 90-degree ladder sections.

Highlights

- Securely connects cable management ladders outside rack enclosure or open frame rack
- Compatible with both straight and 90-degree-bend ladder sections
- Fits solid and tubular steel runway measuring 1.5 x 0.375 in. (38 x 9.5 mm)
- Works with all Tripp Lite SmartRack® ladder system accessories and runways
- Includes all necessary mounting and installation hardware for immediate use

Applications

- Lengthen a ladder runway system outside your data center's rack enclosure or open frame rack

System Requirements

- Compatible with straight and 90-degree-bend ladder sections, including Tripp Lite SRCABLELADDER, SRCABLELADDER18, SRL90BEND12, SRL90BEND18.

Package Includes

- (4) Splice plates
- (2) M10 bolts
- (2) M10 split lock washers
- (2) M10 hex nuts
- Installation guide



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Specifications

OVERVIEW	
UPC Code	037332214461
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / cm)	6.50 x 7.01 x 13.97
Shipping Dimensions (hwd / in.)	2.56 x 2.76 x 5.50
Shipping Weight (kg)	0.44
Shipping Weight (lbs.)	0.96
Unit Dimensions (hwd / cm)	6.6 x 7.11 x 13.97
Unit Dimensions (hwd / in.)	2.6 x 2.8 x 5.5
Unit Weight (kg)	0.38
Unit Weight (lbs.)	0.840
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>