

DATA SHEET



USB-C 2.0 Male to Male Cable (3A)

Connect any two standard USB-C enabled devices to simultaneously charge and transfer data

OVERVIEW

The USB-C to C 2.0 Male to Male Cable is the perfect solution for connecting two standard USB-C enabled devices or accessories for charging and data transfer.

Ensure that a USB-C equipped laptop, smartphone, or tablet is fully charged and ready to go with the 3A charging output, while simultaneously transferring photos, music, or data at speeds up to 480 Mbps.

The USB-C connector has a symmetrical design which is identical on both sides, so no more worrying about whether it's upside-down or right-side-up. It will plug in the first time, every time—while preventing damage to the connector port.

FEATURES

- Longer transfer distance than USB 3.1 Gen 2 cables
- 3A charging output
- Data transfer speeds up to 480 Mbps
- Reversible, symmetrical USB-C connector

ITEM DESCRIPTION

88826	1.8m USB-C 2.0 Male to Male Cable (3A)
-------	--

DATA SHEET


SPECIFICATIONS: USB-C 2.0 Male to Male Cable (3A)

ELECTRICAL SPECIFICATIONS:


- NO—UL 32AWG (7/0.08TC)*1P+32AWG(7/0.08TC)*1C+24AWG (26/0.1TC+25OD)*1C+3E(19/0.05TC+25OD)+AB(16/9/0.06TC 95%TC) OD:3.0mm ~ Black
- Rated Temperature: 80°C ; Voltage: 30 V
- Max Conductor Resistance at 20°C: 32AWG , 530 OHMS/KM
- Insulation Resistance: 10M-KM MIN at 20°C DC 500V.(EIA—364—21)
- Dielectric Strength: AC 500V/1 Minute No Breakdown.(EIA—364—20)

PHYSICAL SPECIFICATIONS:

- Operating Temperature: 0 ~ 50°C; 15-85% RH (Non-Condensing)
- Storage Temperature: -25 ~ 70°C; 15-85% RH (Non-Condensing)
- P1: USB3.1 C Type Male: Contacts Terminal Gold Flash, Nickel Plated Shell; Black Insulation
- P2: USB3.1 C Type Male: Contacts Terminal Gold Flash, Nickel Plated Shell; Black Insulation
- Moulding Material: Black PVC Conform RoHS
- Product is CE marked and conforms to 2011/65/EU RoHS2



CABLE Cross Section.:



Pin Assignment

	P1	P2	
(B4,B9,A4,A9)	VBus	VBus	RED
(A5)	CC	CC	YELLOW
(A7)	D-	D-	WHITE
(A6)	D+	D+	GREEN
(A1,A12,B1,B12)	GND	GND	Drain
	Shell	Shell	Braid

C2G
A brand of **legrand**

Great King Street North
Birmingham, West Midlands B19 2LF
UK Phone (0)800 328 2916
EMEA Phone +44 (0)1952 677300
www.c2g.com/uk

Follow Us

