



## Model 1017-WH

### 10 in. Protective Plastic Box for Wall-Mounted Wi-Fi Access Points / White

Category: **Hi-Bar**



Hotels and residence halls often require APs in each room. Many compact APs fasten to a telecommunications outlet low on the wall, vulnerable to tampering, disconnect, or accidental damage. This compact, non-metallic Hi-Bar™ plastic box protects the AP and cables connected to it. Deep enough to surface mount APs without a telecommunications outlet in the wall, the low-profile 1017 is molded from durable ABS plastic, virtually transparent to the wireless signal. Box cover has tamper-resistant screws.



#### Features & Benefits

- Impact-resistant, ABS plastic protective box in black (1017-BL) or off-white (1017-WH), designed to protect smaller, wall-mounted access points
- Ideal for protecting wireless access points in hotel rooms and residence halls
- Mounts directly over access point attached to the wall, ABS plastic is virtually transparent to wireless signals
- Includes an internal AP standoff bracket, for surface mount applications without telecommunications outlet in the wall
- Tamper-resistant hardware (torx screws) for cover
- Low profile (3.15"); fits behind desks or furniture

#### Technical Specifications

- Design: AP enclosure designed to be surface mounted on hard-lid ceilings or walls. Designed to accommodate smaller wall mount APs with integrated or non-detachable antennas, such as Cisco 702W or Aruba 205H APs
- Performance: Ventilated, impact resistant ABS plastic enclosure is virtually transparent to wireless signals
- Screw on cover with tamper resistant (torx) screws
- Internal universal AP standoff bracket for surface mounting applications without outlet in the wall
- Construction: UL94-5VA classified ABS plastic, Beige body and cover
- External size: 6 x 10.1 x 3.15 in. (152 x 256 x 80 mm). available internal dimensions 5.78 x 9.75 x 2.91 in. (147 x 248 x 69 mm)

#### Standards for Safety

- UL-945VA ABS Material

**Measurements** (Maximum values\*):

- Width: 10.1 in.
- Height: 6 in.
- Depth: 3.15 in.
- Item Weight: 2 lbs.
- Shipping Weight: 9 lbs.





**Includes**

- (1) ABS box and lid
- (1) Internal AP standoff bracket
- (4) AP standoff bracket screws
- (6) #4 x 1/2" Black torx lid screw
- (6) #4 x 1/2" Black Philips lid screw
- (4) #6 x 1/4" Philips AP mounting screw
- (4) #2 x 1/2" Philips mounting bracket screw
- Installation instructions

**3D Interactive Models**

 [Model Viewer at oberoninc.com](#)

**Documentation Links**

-  [Spec Sheet](#) - oberoninc.com/index.php?option=com\_content&view=article&id=2022&Itemid=399
-  [Installation Instructions](#) - oberoninc.com/images/\_Instructions/Oberon\_Model\_1017-WH\_Instructions.pdf
-  [Customer Prints](#) - oberoninc.com/images/\_Customer\_Prints/Oberon\_Model\_1017-WH\_Customer\_Print.pdf
-  [SECTION 27\\_21\\_33 DATA COMMUNICATIONS WIRELESS ACCESS POINTS](#)  
[https://oberoninc.com/images/WebDocs/SECTION\\_27\\_21\\_33\\_DATA\\_COMMUNICATIONS\\_WIRELESS\\_ACCESS\\_POINTS.pdf](https://oberoninc.com/images/WebDocs/SECTION_27_21_33_DATA_COMMUNICATIONS_WIRELESS_ACCESS_POINTS.pdf)



**Additional Information**

 For Oberon product CAD files, contact customer service

**Configurations: Model 1017**

Please specify configuration when ordering.

1017-	
	<b>COLOR</b>
	<b>BK</b> (Black)
	<b>WH</b> (White)

SKU		Description
	1017-BK	Oberon Model 1017, black
	1017-WH	Oberon Model 1017, off-white - minimum order may apply

*Images and documents may depict similar models in the product series.*