

High-Speed HDMI 2.0a Cable, Gripping Connectors - 4K, 60 Hz, 4:4:4, (M/M), Black, 25-ft

MODEL NUMBER: **P568-025-2A**



High-speed 4K HDMI cable connects your laptop or tablet to an HDTV, monitor or projector for crystal-clear 4K video with 4:4:4 color.

Features

4K HDMI 2.0a Cable Connects Home Theater or Digital Signage Audio/Video Components This high-speed HDMI 2.0a cable securely connects HDMI-enabled laptops, tablets, PCs, Blu-ray players, game consoles or satellite/cable TV boxes to HDTVs, HD monitors, projectors or home theater receivers. The 25-foot length allows you great flexibility in placing your home theater components.

Enjoy the Clarity of True 4K HDMI 2.0a Video with Multi-Channel Audio and 4:4:4 Color This Tripp Lite 4K HDMI cable provides a pure digital connection that supports Ultra HD video resolutions up to 3840 x 2160 (4K x 2K) at 60 Hz for crystal-clear picture and sound. It's compatible with HDCP 2.2 and HDMI 2.0a standards for carrying HDR (high dynamic range) signals. It also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor. The cable is backward compatible with previous HDMI generations, allowing you to use it to connect lower-resolution components.

Invest in Quality Construction for Reliable Performance High-quality materials ensure outstanding performance throughout the cable's lifetime. Contacts and connectors are gold-plated to resist corrosion. Double shielding reduces line noise (EMI/RFI) that can disrupt signals traveling through the HDMI cord.

Highlights

- Delivers UHD picture quality at resolutions up to 3840 x 2160 (4K x 2K) @ 60 Hz
- Supports 4:4:4 chroma subsampling for HDR-compatible televisions
- 25 ft. length allows great flexibility in setting up devices in your home theater
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Watch 4K video content from a Blu-ray player, game console, laptop or tablet on an Ultra HD television, monitor or projector
- Connect a Chromebook or MacBook to a conference table's A/V box to give a video presentation on a large screen
- Play online or PC video games that display optimal graphics
- Attach an HDTV to your PC for use as a 4K monitor
- Combine with an Apple digital A/V adapter to support iPad2 video mirroring
- Send Ultra HD content to digital signs or point-of-sale displays

Package Includes

- P568-025-2A High-Speed HDMI 2.0a Cable, M/M, 25 ft.

Specifications



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

OVERVIEW	
UPC Code	037332236777
INPUT	
Cable Length (ft.)	25
Cable Length (m)	1
Cable Length (in.)	300
Product Length (in.)	300
Product Length (ft.)	25
PHYSICAL	
Cable Jacket Type	PVC
Cable Outer Diameter (OD)	10.0 +/- 0.2mm
Color	Black
Material of Construction	PVC
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Weight (kg)	0.78
ENVIRONMENTAL	
Operating Temperature Range	14°F to 122°F (-10° ~ 50°C)
Storage Temperature Range	5°F to 140°F (-15° ~ 60°C)
Relative Humidity	0% to 90% Non Condensing
CONNECTIONS	
Side A - Connector 1	HDMI (MALE)
Side B - Connector 1	HDMI (MALE)
FEATURES & SPECIFICATIONS	
Max Supported Video Resolution	3840 x 2160 (4K @ 60HZ 4:4:4)
HDMI Specification	2.0a
HDCP Specification	2.2
Technology	HDMI; HDR
STANDARDS & COMPLIANCE	
Certifications	Tested to RoHS
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
----------------------------------------	---------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>