






## Model 39-1020-PMK Pole Mount Kit for Oberon Model 1020-RAB

Category: **WiTile**



The Model 39-1020-PMK is a pole mount kit designed to Oberon's Model 1020-RAB to square and round poles.



### Features & Benefits

- Adjustable worm gear clamps for square and round poles with diameters from 5" to 9"
- Designed to mount Oberon Model 1020-RAB vertically and horizontally
- Opening for cable egress

### Technical Specifications

- Light gray powder-coated aluminum with stainless steel hardware
- Size: 11" x 4" x 1.9" deep
- Shipping Weight: 5 lbs.

### Measurements (Maximum values\*):

- Width: 4 in.
- Height: 11 in.
- Depth: 1.9 in.
- Item Weight: N/A
- Shipping Weight: 5 lbs.


### Includes

- (1) Pole Mount Bracket
- (2) Worm gear clamps
- (4) #10-32 stainless steel screws
- (1) Installation instructions

### Documentation Links

[https://oberoninc.com/images/WebDocs/SECTION\\_27\\_21\\_33\\_DATA\\_COMMUNICATIONS\\_WIRELESS\\_ACCESS\\_POINTS.pdf](https://oberoninc.com/images/WebDocs/SECTION_27_21_33_DATA_COMMUNICATIONS_WIRELESS_ACCESS_POINTS.pdf)








**Additional Information**

 For Oberon product CAD files, contact customer service

**Configurations: Model 1020**

Please specify configuration when ordering.

|       |  |  |  |
|-------|--|--|--|
| 1020- |  |  |  |
|       | <b>LID STYLE</b><br>00 (Solid Grey)<br>C (Clear) | <b>BRACKET STYLE</b><br>RAB (Right Angle)<br>USM30 (30° Under Seat)<br>(otherwise leave blank) | <b>MOUNT STYLE</b><br>PMK (Pole Mounting Kit, with -RAB only)<br>(otherwise leave blank) |

| SKU  | Description   |
|--|---|
|  1020-00           | Polycarbonate NEMA 4 AP Enclosure: Screw-on cover                 |
|  1020-C           | Polycarbonate NEMA 4 AP Enclosure: Screw-on clear cover           |
|  1020-00-RAB     | NEMA 4 AP Enclosure: Screw-on cover, Right-angle                  |
|  1020-C-RAB      | NEMA 4 AP Enclosure: Screw-on clear cover, Right-angle            |
|  1020-00-RAB-PMK | NEMA 4 AP Enclosure: Screw-on cover, Right-angle pole mount       |
|  1020-C-RAB-PMK | NEMA 4 AP Enclosure: Screw-on clear cover, Right-angle pole mount |
|  1020-00-USM30   | NEMA 4 AP Enclosure: Screw-on cover                               |

*Images and documents may depict similar models in the product series.*