

A/V Cables



PROFESSIONAL GRADE A/V SOLUTIONS FROM ONE SOURCE

The On-Q line of Professional Grade Audio/Video cables & accessories provides everyday project support from an extensive line of code compliant products, all from a single one-stop shop.

With bulk packs and included CTA 863 color bands, On-Q gives you everything you need to meet standards and get your job done quickly:

- **Universal 1, 2, & 3 Cables**
- **Toslink**
- **Composite video**
- **5mm**



FEATURES

- U.L. Tri-Rated (CMG/CLx/FT4) for code compliant in-wall installation*
- Included color bands with Universal products match the CTA 863 Home Theater Color Code specification to reduce support by both the distributor and installer
- All 3.5mm cables, including adapters, feature "CaseConnect" a standoff that allows for a secure connection through most mobile device cases

*Excludes adapter products

BENEFITS

- Code compliant cables offer safe, in-wall installation
- Easily plug in without removing device cases and covers with "CaseConnect" for a secure, strong signal

Cable SPEC (with applicable notes):	MINIMUM Construction	Cable Jacket	Agcy	Color	Connector		Feet	Legrand P/N:	Notes:
Universal 3 Cable (Component)	28 AWG Stranded	CL2	UL	Cable Blk	Gold	Overmold White	3ft	AC2303-BK	Boots will come pre-configured with R/G/B color bands; each assembly will come with 8 additional color bands loose in polybag (qty 2 Yellow, qty 2 White, qty 2 Purple, qty 2 Orange)
							6ft	AC2306-BK	
							12ft	AC2312-BK	
							25ft	AC2325-BK	
Universal 2 Cable (L/R Audio)	28 AWG Stranded	CL2	UL	Cable Blk	Gold	Overmold White	3ft	AC2203-BK	Boots will come pre-configured with R/W color bands; each assembly will come with 6 additional color bands loose in polybag (qty 2 Yellow, qty 2 Purple, qty 2 Orange)
							6ft	AC2206-BK	
Universal 1 Cable (Subwoofer)	RG59/U	CMG, CL2, FT4	UL	Cable Blk	Gold	Overmold White	3ft	AC2103-BK	Boots will NOT come pre-configured; Comes with 6 color bands in polybag (qty 2 Yellow, qty 2 Purple, qty 2 Orange)
							6ft	AC2106-BK	
							12ft	AC2112-BK	
							25ft	AC2125-BK	
Composite with L/R	RG59/U-28AWG	CL2	UL	Cable Blk	Gold	Overmold (Y/R/W)	6ft	AC2006-BK	
							12ft	AC2012-BK	
Toslink	5.0 mm OD	CMG, CL2, FT4	UL	Cable Blk	-- --	Overmold Black	3ft	AC2403-BK	Comes With Pair of Toslink to Mini Toslink Adapters
							6ft	AC2406-BK	
							12ft	AC2412-BK	
							25ft	AC2425-BK	
Stereo 3.5 mm to L/R Audio (with Case Connect)	28 AWG Stranded	CL2	UL	Cable Blk	3.5mm Nickel RCA Gold	Overmold (Blk/R/W)	6ft	AC2706-BK	
							12ft	AC2712-BK	
	24 AWG Stranded						25ft	AC2725-BK	
Stereo 3.5 mm to 3.5mm - M/M (with Case Connect)	28 AWG Stranded	CMG, CL2, FT4	UL	Cable Blk	Nickel	Overmold Blk	6ft	AC2606-BK	
							12ft	AC2612-BK	
	24 AWG Stranded						25ft	AC2625-BK	
Stereo 3.5 mm to 3.5mm - M/F (with Case Connect)	28 AWG Stranded	CMG, CL2, FT4	UL	Cable Blk	Nickel	Overmold Blk	6ft	AC2506-BK	
							12ft	AC2512-BK	
Stereo 3.5 mm Y M/2F (with Case Connect)	28 AWG Stranded	---	---	Cable Blk	Nickel	Overmold Blk	6in	AC2501-BK	
RCA Y M/2F	28 AWG Stranded	---	---	Cable Blk	Gold	Overmold (Blk/R/W)	6 in	AC2701-BK	
RCA Y F/2M	28 AWG Stranded	---	---	Cable Blk	Gold	Overmold (Blk/R/W)	6 in	AC2702-BK	
RCA Coupler (Pair)	---	---	---	---	Gold	Overmold Blk	-- --	AC2704-BK	

designed to be better™



Legrand, North America

60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca