



\sim	
\sim \sim \sim	-IN
- リンノレ	

NETWORK CENTERS

FRASTRUCTURE/Enclosures

PRODUCT	PART#	DESCRIPTION	DIMENSIONS
Advanced Network Center, Surface Mount	364398-02	Distributes incoming video signals for up to six television outlets and supports up to 11 telephone outlets with up to four phone lines. Surface-mount design is ideal for retrofit applications. Network center features two expansion bays for additional modules.	19" H x 7" W
PRODUCT	PART #	DESCRIPTION	DIMENSIONS
Basic Network Center	364397-01	Basic network center distributes incoming video signals to up to four television outlets and supports up to six telephone outlets with up to four phone lines. It's an economical solution for small, fixed installations. Surface mount design is ideal for retrofit applications.	19" H x 7" W
PRODUCT	PART#	DESCRIPTION	DIMENSIONS
Trio Modular Bracket and Cover	F7804	The Trio bracket features a rugged, enamel- finished steel housing that includes an impact- resistant cover. It conveniently mounts on a plywood backboard.	11.6" H x 4.8" W x 4" D
PRODUCT	PART #	DESCRIPTION	DIMENSIONS
Trio Home Network Kit	F7809	Kit includes a low cost, surface-mounting bracket that's ideal for small or retrofit installations. It	11.6" H x 4.8" W x 4" D

NETWORK CENTERS

PRODUCT	PART#	DESCRIPTION	DIMENSIONS
Universal Network Center	364399-01	Ideal for new construction and features three expansion bays for additional modules.	19" H x 7" W
Basic Network Center Cover	364393-01	Conceals and protects cables.	10" H x 7" W
Advanced Network Center Surface Mount Cover	364394-01	Protects contents of advanced network center.	19" H x 7" W

ENCLOSURES

Description	14" Enclosure	20" Enclosure	28" Enclosure	42" Enclosure	20" Rough-In	26" Rough-In	36" Rough-In
Page Number	18	18	19	19	21	21	21
Dimensions	14" H x 14.25" W x 3.6" D	20" H x 14.25" W x 3.6" D	28" H x 14.25" W x 3.6" D	42" H x 14.25" W x 3.6" D	19.5" H x 14.2" W x 4.6" D	26" H x 19.1" W x 3.6" D	36" H x 19.1" W x 3.6" D
Cover/Door	Hinged or Screw-On Optional						
UL Listed	Yes						
Allows Surface or Recessed Mounting	Yes	Yes	Yes	Yes	Recessed Only	Recessed Only	Recessed Only
Allows Left and Right Module Mounting	Yes						
Enclosure Extender	No	No	Yes	Yes	No	No	No
AC Outlet Knockout	Yes						
Cable Guard Insert Included	Yes						
Cable Management Tie Downs	Yes						
Conduit Knockout	Optional	Optional	Optional	Optional	Yes	Yes	Yes

ENCLOSURE ACCESSORIES

PRODUCT	PART#
Single Bay Video Bracket	AC1007
Single Bay Bracket	364890-01
Two Bay Bracket	364819-01
Three Bay Bracket	F7510
Six Bay Bracket	F9001
Pins & Rivets for Mounting F7520 & F7510 (Bag of 50)	F2250

PRODUCT	PART#
Blank Plate for Unused Module Spaces	F7717
Grommet Ring	F2242
2.5" Knockout Plug	F2249
Replacement Key Kit - Hinged Enclosure	364490-01
Replacement Lock Assembly - Hinged Door	364478-01
Custom Wire Management Module	364570-01