## KIP640/642/643/646/ 647/648/649/655(-S)





## Wall Kiosk Enclosure

Fits 40", 42", 43", 46", 47", 48", 49" and 55" Displays up to 2" (50mm) Thick


Peerless-AV's Wall Kiosk Enclosure provides a sleek digital showcase for advertising, entertaining, interactive wayfinding, and much more. These innovative kiosk enclosures accommodate a wide variety of ultra-thin displays in either landscape (KIL models) or portrait (KIP models) orientation. Despite the slim, ADA-compliant 3.97" profile, the kiosk enclosure can easily house media players, fans and other electrical equipment needed to create an impressive digital solution. From hotels to casinos to movie theaters, Peerless-AV's Wall Kiosk Enclosures are ideal for applications that want to take the guest experience up a notch and differentiate their brand.

Peerless-AV's Wall Kiosk Enclosure is the ideal digital signage platform to fully engage guests.

### **Additional Features**

- Eight way tool-less adjustment to quickly position display in kiosk window for flush alignment
- ✓ VESA® 200 x 200 up to 400 x 600mm compatible
- Thermostat controlled circulation fans ensure proper airflow within the kiosk
- Low profile design extends 3.97" (101mm) away from the wall, which meets the Americans with Disabilities Act (ADA) certification requirements
- Hinged top frame offers easy access to the display and other internal components for easy maintenance and enhanced security
- Supports wide range of aesthetic options including glass/acrylic, multiple colors, vinyl wraps, etc. to best match environment or promote brand strategy
- Pre-assembled to simplify installation of the entire solution
- Custom sizes available for smaller and larger displays

# HINGED LOCKING FRAME Highly secure frame hinges open for easy installation and maintenance access PULL OUT MOUNT Allows for easy installation, adjustment and maintenance of the display



Prevents unintended access to inside of kiosk enclosure



Landscape models available



Pull out mount for easy installation of display





### **Model Numbers**

### WARRANTY: 5 years on metal components, 1 year on electronic components

Portrait Models:

KIP640(-S)	Wall Kiosk Enclosure fits 40" Displays up to 2" (50mm) Thick	KIP647(-S)	Wall Kiosk Enclosure fits 47" Displays up to 2" (50mm) Thick
KIP642(-S)	Wall Kiosk Enclosure fits 42" Displays up to 2" (50mm) Thick	KIP648(-S)	Wall Kiosk Enclosure fits 48" Displays up to 2" (50mm) Thick
KIP643(-S)	Wall Kiosk Enclosure fits 43" Displays up to 2" (50mm) Thick	KIP649(-S)	Wall Kiosk Enclosure fits 49" Displays up to 2" (50mm) Thick
KIP646(-S)	Wall Kiosk Enclosure fits 46" Displays up to 2" (50mm) Thick	KIP655(-S)	Wall Kiosk Enclosure fits 55" Displays up to 2" (50mm) Thick

## **Product Specifications**

	DIMENSIONS (W x H x D)	PRODUCT WEIGHT	LOAD CAPACITY	FINISH	AVAILABLE COLORS
KIP640/642/643(-S)	27.10" x 44.24" x 3.94" (688 x 1124 x 100mm) 29.10" x 48.16" x 3.94"	62.6lb (28kg)	75lb	Powder	KIP640/642/643/646/647/648/649/655: Gloss black
KIP646/647/648(-S)	(739 x 1223x 100mm)	67.8lb (30kg)	(34kg)	Coat	
KIP649/655(-S)	33.50" x 55.07" x 3.94" (861 x 1399 x 100mm)	79.5lb (36kg)			KIP640-S/642-S/643-S/646-S/647-S/648-S/649-S/655-S: Silver

### **Package Specifications**

	PACKAGE SIZE (W x H x D)	PACKAGE SHIP WEIGHT	PACKAGE UPC CODE	PACKAGE CONTENTS	UNITS IN PACKAGE
KIP640/642/643(-S) KIP646/647/648(-S) KIP649/655(-S)	50.00" x 36.00" x 8.00" (1270 x 914 x 203mm) 54.00" x 39.00" x 8.00" (1371 x 990 x 203mm) 62.00" x 43.00" x 8.00" (1574 x 1092 x 203mm)	85lb (39kg) 95lb (43kg) 105lb (48kg)	KIP640: 735029296874 KIP640-S: 735029296935 KIP642: 735029297451 KIP642-S: 735029297468 KIP643: 735029315735 KIP643-S: 735029315766 KIP646: 735029296881 KIP646-S: 735029296942 KIP647: 735029296898 KIP648-S: 735029296966 KIP648: 735029307990 KIP648-S: 735029308003 KIP649: 735029318712 KIP649-S: 735029318798 KIP655: 735029308102 KIP655-S: 735029309199	Kiosk with display mounting hardware	1

### **Accessories**

ACC415: 4-pack Metal Stud Fastener Kit

CL-SCG200: Screen Cleaning Gel

DEB-HD10: 32' (10m) High Speed HDMI® Cables with Ethernet

PVP1000-PL6: Surge Protector with Six Outlets

### KioskBuilder™:

Build your own Integrated Kiosk @ kiosks.peerless-av.com including integration services, flat panel display, media player, content management software, power protection, thermal management, display protection, vinyl graphics, etc.





### Agion antimicrobial protection:

Agion® antimicrobial\* finish available to assist in controlling the spread of infections. Contact Peerless-AV Customer Care for more information.

\*Antimicrobial protection is limited to the treated article and does not protect a user against disease causing bacteria. Always clean products thoroughly after each use.

All dimensions = inch (mm)





MODEL NO.	DIMENSION "A"	DIMENSION "B"	DIMENSION "C"	DIMENSION "D"	DIMENSION "E"
KIP640	27.10" (688mm)	3.94" (100mm)	44.24" (1124mm)	19.67" (500mm)	34.97"(888mm)
KIP642	27.10" (688mm)	3.94" (100mm)	44.24" (1124mm)	20.65" (525mm)	36.72" (933mm)
KIP643	27.10" (688mm)	3.94" (100mm)	44.24" (1124mm)	21.13" (537mm)	37.59" (955mm)
KIP646	29.10" (739mm)	3.94" (100mm)	48.16" (1223mm)	22.61" (574mm)	40.20" (1021mm)
KIP647	29.10" (739mm)	3.94" (100mm)	48.16" (1223mm)	23.10" (587mm)	41.07" (1043mm)
KIP648	29.10" (739mm)	3.94" (100mm)	48.16" (1223mm)	23.59" (599mm)	41.94" (1065mm)
KIP649	33.50" (851mm)	3.94" (100mm)	55.07" (1399mm)	24.08" (611mm)	42.82" (1087mm)
KIP655	33.50" (851mm)	3.94" (100mm)	55.07" (1399mm)	27.03" (686mm)	48.05" (1220mm)

### **Architect Specifications**

The Wall Kiosk Enclosure shall be a Peerless-AV model KIP640(-S), 642(-S), 643(-S), 646(-S), 647(-S), 648(-S), 649(S) or 655(-S) and shall be located where indicated on the plans. Assembly and installation shall be done according to instructions provided by the manufacturer.

Visit peerless-av.com to see the complete line of AV solutions from Peerless-AV, including outdoor displays, wireless, kiosks, digital audio, display mounts, projector mounts, carts/stands, and a full assortment of accessories.

### Peerless-AV

2300 White Oak Circle Aurora, IL 60502 USA

(800) 865-2112 (630) 375-5100 Fax: (800) 359-6500

### Peerless-AV Europe

Unit 3 Watford Interchange Colonial Way, Watford Herts, WD24 4WP United Kingdom

+44 (0) 1923 200100 Fax: +44 (0) 1923 200101

Peerless-AV de México Ave de las Industrias 413 Parque Industrial Escobedo Escobedo, N.L., Mexico 66050

+52 (81) 8384-8300 Fax: +52 (81) 8384-8360

