

Planar SL7564K

4K LCD Display

The Planar® Simplicity™ Series SL7564K is a 75" 4K LCD display for digital signage that incorporates media playback, 4K @ 60Hz support, HDCP2.2 compliance and commercial functionality into an affordable 75" digital signage solution. Its elegant design with a narrow, logo-free bezel, slim profile and integrated OPS slot provide the ideal display solution for digital signage applications in retail stores, restaurants, medical offices, corporate meeting areas and hospitality.



SPECIFICATION	DETAIL
Product Name	SL7564K
Planar Part Number	997-9407-00
Display Resolution	Ultra HD (3840 x 2160)
HD format	4K UHD 2160p
Screen Size	75 in. (diagonal)
Aspect Ratio	16:9
Display Technology	Edge-lit LED LCD
Haze	3%
Display Active Area	65.0" x 36.5" (1650mm x 928mm)
Viewing Angle (typ)	178°
Backlight	LED
Brightness (typ)	410 nits
Response Time (typ)	8 ms
Frame Rate	60Hz
Contrast Ratio (typ)	1200:1
Pixel Pitch	0.429mm x 0.429mm
Color Gamut	72% NTSC
Display Color	>1 billion colors. Full 10 bit data path
External Connections	HDMI 2.0 x 4 (HDCP 2.2), DisplayPort x 1, VGA x 1, OPS x 1, OPS USB 2.0 x 2, OPS USB 3.0 X 1
Modes	3840x2160 @ 24/25/30/60Hz; 480p, 576p, 720p @ 50/60 Hz; 1080p @ 50/60Hz; 1080i @ 50/60 Hz
Display Control	IR, RS-232, LAN, Keypad

Cabinet Dimensions (W x H x D)	66.0" x 37.6" x 2.5" (1676.6mm x 955.0mm x 62.8mm)
Cabinet Dimensions with Handles (W x H x D)	66.0" x 37.6" x 2.9" (1676.6mm x 955.0mm x 73.8mm)
Orientation	Landscape only
Bezel Width	0.5" (12.5mm)
Weight	118 lb (53 kg)
Weight (Shipping)	145 lbs (66 kg)
Audio	PC Line in, RCA L/R out
Speakers	10W x 2 built-in
Mounting	VESA: 600mm x 400mm
Fanless	Yes
Line Voltage	100-240V; 50/60Hz
Power Consumption (typ)	215W (standby: <0.5W)
Operating Temperature	0° to +40°C (32° to 104°F) up to 3000m
Humidity	20 - 85% RH (non-condensing)
Options / Features	USB playback with scheduling, logo-free bezel, lockable rear keypad, OPS slot
Approvals	FCC Class A, CE, cTUVus, CCC
Warranty	2 years
Recommended Usage	Up to 16 hours per day
In the Box	SL7564K display, C14 connector power cord, HDMI cable, RS-232 cable, IR cable, remote control, and cable clamps
UPC	8 10689 00505 6

For more information, please visit www.planar.com

Specifications are subject to change without notice.

Specification Report Date: 11/28/2019

© Copyright 2019 Planar Systems, Inc. All rights reserved