

AXIS S9002 Mk II

Effective 4K client for server installations

AXIS Camera Station S9002 Mk II Desktop Terminal is an easy-to-install desktop terminal for high-definition surveillance with support for four simultaneous 4K streams. The terminal is preloaded with AXIS Camera Station client and all necessary software and is preconfigured to minimize installation time. With its slim form factor, AXIS S9002 Mk II complements Axis rack servers to create a high-end surveillance workstation. The terminal has validated hardware components, such as graphic card and CPUs and supports four monitors for optimal system overview. AXIS S9002 Mk II includes a 5-year warranty, a keyboard and computer mouse.

- > Ease of installation
- > AXIS Camera Station client included
- > Validated high performing hardware
- > High-definition surveillance up to four 4K streams
- > Extensive support







www.cxis.com T10131871/EN/M9.2/2010

AXIS S9002 Mk II

Hardware	
	Intol® CovoTN :F
Processor	Intel® Core™ i5
Memory	8 GB
Graphic card	Nvidia® Quadro®
Power	300 W (100 - 240 V AC, 50/60 Hz, 4.2 - 2.1 A)
Connectors	5x USB 3.1 1x USB 3.1 Type-C 4x USB 2.0 4x Mini DisplayPort™ 1.2 (not preferred) 4x Mini DisplayPort™ 1x Ethernet (RJ45) 1 GbE 1x Universal audio jack) 1x Audio line out 1x Serial port PS2 Mouse and keyboard ports
Video	
Video streaming	Live view: 4 monitors x 4K full screen at 25 fps 4 monitors x 4 split x 1080p at 20 fps 4 monitors x 9 split x 720p at 15 fps Playback: Limited to 1 monitor but supports the same split scenarios as for live view.
General	
Operating system	Microsoft® Windows® 10 IoT Enterprise SAC Built-in operating system recovery: yes

	Operating system drive: 128 GB SSD
Operating conditions	0 °C to 45 °C (32 °F to 113 °F)
Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F)
Approvals	EMC EN 55032, EN 55024, EN/IEC 61000-3-2, EN/IEC 61000-3-3, EN 50564, EN 62623, FCC Part 15 Subpart B Class B, ICES-003 Class B, VCCI Class B, RCM AS/NZS CISPR 32 Class B, KC KN32 Class B, KN35, Safety IEC/EN/UL 60950-1, NOM, BSMI, EAC
Dimensions	292 x 93 x 290 mm (11.5 x 3.67 x 11.42 in)
Weight	5.0 kg (11 lb)
Included accessories	Keyboard (international/US), mouse, 4 x Mini DisplayPort™ to DisplayPort™ adapters
Optional accessories	Axis joysticks and control boards For more accessories, see axis.com
Warranty	5-year warranty, see axis.com/warranty

Environmental responsibility:

axis.com/environmental-responsibility

