

PD-9601GO Midspan

Single Port, 90W, Outdoor PoH Midspan

Overview

Microsemi's PD-9601GO is a 90W single-port Midspan offering a cost effective, PoH compliant solution for outdoor installations, guaranteeing 90 Watts of power and ensuring safe and reliable operation in outdoor environment of any standard PoH data terminal. It allows wireless LAN access points, security network cameras and other IP terminals to receive power, along with data, over standard Ethernet cables, leaving network infrastructure completely unaltered. The PD-9601GO also offers surge protection for both the AC and the PoE ports ensuring the indoor equipment is protected from outdoor surges.

Key Features

- Up to 90W of power over 4-pair
- Outdoor rated: IP66
- Extended temperature range -40°C to +65°C
- Power provided using all 4 pairs
- Supports 10/100/1000Mbps data rates
- Plug 'n Play installation (installer does not have to open unit)
- Supports both 802.3af and 802.3at Powered devices
- Includes integral surge protection



Specifications

Feature	Description
No. of Ports	1
Data Rates	10/100/1000 Mbps
Power over Ethernet Output	4/5 (+), 7/8 (-), 1/2(-), 3/6(+) Output Power Voltage: 54 VDC
User Port Power	90 Watts (Guaranteed)
Input Power Requirements	AC Input Voltage: 100-240Vac ±10% AC Input Current: 2.5A @ 100Vac AC Frequency: 50 to 60Hz
Dimensions	214 mm x 150 mm x 70 mm 8.42 in. x 5.90 in. x 2.75 in
Weight	4.85 lbs (2.2Kg)
Connectors	Shielded rugged RJ-45 (with gasket)
Environmental Conditions	Operating Ambient Temperature: -40° to 149°F (-40 to 65°C)
	Operating Humidity: Maximum 95%, Non-condensing
	Storage Temperature: -40° to 158°F (-40° to 85°C)
	Storage Humidity: Maximum 95%, Non-condensing
	Operating Altitude Up to 6,560 ft. (2000 m)
Reliability	MTBF: 189,000 hrs. @ 25°C
Weather Rating	IP66, NEMA 4X
Thermal Rating	41 BTU/Hr (@240VAC)
Warranty	1-year
Regulatory Compliance	IEEE 802.3af (PoE, PoH Type1) IEEE 802.3at (PoE+ including 2-event, PoH Type 2), RoHS Compliant, WEEE Compliant, CE
Electromagnetic Emission & Immunity	FCC Part 15, Class B EN 55022 Class B EN 55024 VCCI
Surge Protection	Meets Surge Protection as specified in GR-1089-CORE Issue 6 ITU-T K.20 6 kV on AC lines
Safety	UL/IEC/EN 60950-1 UL-69950-22
Other Standards and	Dust and water intrusion: EN60529
Approvals	Level1P66; NEMA 250, Level 4X ASTM B-117 Corrosion Resistance

PD-9601GO Midspan

Single Port, 90W, Outdoor PoH Midspan

Ordering Information

Microsemi p/n	Name	Description
PD-9601GO/AC	Microsemi PD-9601GO	Single Port, Outdoor PoH Midspan

Microsemi makes no warranty, representation, or guarantee regarding the information contained herein or the suitability of its products and services for any particular purpose, nor does Microsemi assume any liability whatsoever arising out of the application or use of any product or circuit. The products sold hereunder and any other products sold by Microsemi have been subject to limited testing and should not be used in conjunction with mission-critical equipment or applications. Any performance specifications are believed to be reliable but are not verified, and Buyer must conduct and complete all performance and other testing of the products, alone and together with, or installed in, any end-products. Buyer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is the Buyer's responsibility to independently determine suitability of any products and to test and verify the same. The information provided by Microsemi hereunder is provided "as is, where is" and with all faults, and the entire risk associated with such information is entirely with the Buyer. Microsemi does not grant, explicitly or implicitly, to any party any patent rights, licenses, or any other IP rights, whether with regard to such information itself or anything described by such information. Information provided in this document is proprietary to Microsemi, and Microsemi reserves the right to make any changes to the information in this document or to any products and services at any time without notice.



Microsemi Corporate Headquarters
One Enterprise, Aliso Viejo, CA 92656 USA
Within the USA: +1 (800) 713-4113
Outside the USA: +1 (949) 380-6100
Sales: +1 (949) 380-6136
Fax: +1 (949) 215-4996
email: sales.support@microsemi.com
www.microsemi.com

Microsemi Corporation (MSCC) offers a comprehensive portfolio of semiconductor and system solutions for communications, defense & security, aerospace and industrial markets. Products include high-performance and radiation-hardened analog mixed-signal integrated circuits, FPGAs, SoCs and ASICs; power management products; timing and synchronization devices and precise time solutions, setting the world's standard for time; voice processing devices; RF solutions; discrete components; security technologies and scalable anti-tamper products; Ethernet solutions; Power-over-Ethernet ICs and midspans; as well as custom design capabilities and services. Microsemi is headquartered in Aliso Viejo, Calif., and has approximately 3,600 employees globally. Learn more at www.microsemi.com.

©2015 Microsemi Corporation. All rights reserved. Microsemi and the Microsemi logo are registered trademarks of Microsemi Corporation. All other trademarks and service marks are the property of their respective owners.