


1008140230

## TA-23

Industrial Handset for Turbine with PTT

 **ICX-AlphaCom** **Exigo** **IP66**

### DESCRIPTION

#### FEATURES

- Rugged handset for Industrial application
- PTT-key for simplex operation in extremely noisy environments
- Noise-cancelling microphone
- High quality digital background noise reduction\*
- HD-voice compatible\*
- IP Rating: IP66
- Designed for Turbine Industrial Intercoms

\*when used with Turbine Industrial intercoms

#### DESCRIPTION

The TA-23 Industrial Handset for Turbine intercoms is a rugged, high quality handset designed for industrial and military use. The slim profile offers ease-of-use in hard-hat areas as it slips under helmets and/or hearing protection. The TA-23 offers a side-mounted PTT for simplex operation in extremely noisy environments. Used with Turbine industrial intercom stations, the active noise-reduction features offer exceptional audio quality and intelligibility. A hanger is included with the delivery.

## SPECIFICATIONS

### MECHANICAL

Dimensions (WxDxH)	200 x 70 x 50 mm
Weight	310 g
Cable Length	1.0 m (contracted) / 3.5 m (extended)


### ENVIRONMENTAL

Operating Temperature	-40°C to +65°C
Ingress Protection (IP)	IP66

### ACOUSTICAL

Frequency Response	200 - 7000 Hz
--------------------	---------------

## TECHNICAL DIMENSIONS



## USED WITH

1008122010

TFIE-1

IP and SIP Intercom

Created: 04.03.2015, updated: 19.11.2020

page 2/3

[www.zenitel.com](http://www.zenitel.com)

[info@zenitel.com](mailto:info@zenitel.com)

Zenitel and its subsidiaries assume no responsibility for any errors that may appear in this publication, or for damages arising from the information therein. Zenitel products are developed and marketed by Zenitel. The company's Quality Assurance System is certified to meet the requirements in NS-EN ISO 9001. Zenitel reserves the right to modify designs and alter specifications without notice.

ZENITEL PROPRIETARY. This document and its supplementing elements, contain Zenitel or third party information which is proprietary and confidential. Any disclosure, copying, distribution or use is prohibited, if not otherwise explicitly agreed in writing with Zenitel. Any authorized reproduction, in part or in whole, must include this legend; Zenitel – All rights reserved.



1008122020

**TFIE-2**

IP and SIP Intercom



1023201201

**EAPII-1**

Exigo Industrial Access Panel, 1 Button



1023201206

**EAPII-6**

Exigo Industrial Access Panel, 6 Buttons



1008122060

**TFIE-6**

IP and SIP Intercom

