

PanZone® Hinged Wall Mount Bracket

specifications

The hinged wall mount bracket shall be used to mount networking equipment on the wall. The bracket shall have a width of 20.2" and be capable of mounting EIA 19" rack mountable products, including but not limited to, cover panels, fiber panels, etc. The mounting bracket shall be constructed of steel and have mounting holes for #12-24 thread type.



Hinged Wall Mount Bracket

1 RU:	WBH1
2 RU:	WBH2
3 RU:	WBH3
4 RU:	WBH4
4 RU extended depth:	WBH4E
6 RU extended depth:	WBH6E

technical information

Dimensions:	Part Number	RU	Height in. (mm)	Width in. (mm)	Depth in. (mm)
	WBH1	1 RU	1.57 (44.45)	20.2 (513)	6.26 (159.12)
	WBH2	2 RU	3.50 (88.90)	20.2 (513)	6.26 (159.12)
	WBH3	3 RU	5.25 (133.35)	20.2 (513)	6.26 (159.12)
	WBH4	4 RU	7.00 (177.80)	20.2 (513)	6.26 (159.12)
	WBH4E	4 RU	7.00 (177.80)	20.4 (518.7)	15.8 (401.5)
	WBH6E	6 RU	10.5 (266.7)	20.4 (518.7)	15.8 (401.5)

Load capacity:	Part Number	lbs. (kg)
	WBH1	10 (4.53)
	WBH2	20 (9.07)
	WBH3	30 (13.60)
	WBH4	40 (18.14)
	WBH4E	40 (18.14)
	WBH6E	60 (27.21)

Packaging: Bracket is packaged with #12-24 threaded inserts

key features and benefits

Low profile	Provides an efficient way to expand telecommunications equipment in a small, on wall, application
Simple deployment	One person install allows quick and easy install.


applications

The PanZone® Hinged Wall Mount Bracket expands rack space to the wall to maximize space in telecommunications rooms. This hinged wall mount bracket can be used with other Panduit accessories such as patch panels and fiber trays to achieve an open

wall mount rack application for patching or small active equipment.

Panduit is not just a brand, but a promise to bring quality products that efficiently and effectively support your network infrastructure.

PanZone® Hinged Wall Mount Bracket



Dimensions are in inches (Dimensions in brackets are metric).

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
 Phone: 800.777.3300

PANDUIT EUROPE LTD.
 London, UK
 Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
 Republic of Singapore
 Phone: 65.6305.7575

PANDUIT JAPAN
 Tokyo, Japan
 Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
 Guadalajara, Mexico
 Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
 Victoria, Australia
 Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
 or by phone: 800.777.3300

© 2021 Panduit Corp.
 ALL RIGHTS RESERVED.
 ZCSP43--WW-ENG
 1/2021