



## APC NetShelter SX 48U 750mm Wide x 1070mm Deep Enclosure Freestanding rack Black

**Brand :** APC

**Product code:** AR3157

**Product name :** NetShelter SX 48U 750mm Wide x 1070mm Deep Enclosure

NetShelter SX 48U 750mm Wide x 1070mm Deep Enclosure

APC NetShelter SX 48U 750mm Wide x 1070mm Deep Enclosure Freestanding rack Black:

Tall and wide enclosure with 48U spaces for additional equipment and increased cable management options for high density server and networking applications.

APC NetShelter SX 48U 750mm Wide x 1070mm Deep Enclosure. Type: Freestanding rack, Rack capacity: 48U, Maximum weight capacity: 1704 kg. Weight: 169.1 kg. Product colour: Black



Features		Weight & dimensions	
Rack capacity *	48U	Height	2258 mm
Type *	Freestanding rack	Weight	169.1 kg
Maximum weight capacity *	1704 kg	Mounting depth (min)	26.2 cm
Maximum weight capacity (rolling)	1022 kg	Mounting depth (max)	91.5 cm
Product colour	Black	<b>Packaging data</b>	
<b>Weight &amp; dimensions</b>		Package weight	184.1 kg
Size (imperial)	48.3 cm (19")	<b>Other features</b>	
Width	750 mm	Dimensions (WxDxH)	750 x 1070 x 2258 mm
Depth	1070 mm	Package dimensions (WxDxH)	895 x 1219 x 2400 mm
		Dynamic load	1022
		Static load	1704



731304236368

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 01-MAR-2022. Prints or copies of Information are only valid on the printed Publication date