



SPECIFICATION SHEET

STYLE: 280-HP1491RVM



Traverse™

Vented, Industrial Climbing Helmet with Mips® Technology, Polycarbonate/ABS Shell, EPS Foam Impact Liner, HDPE Suspension, Wheel Ratchet Adjustment and 4-Point Chin Strap

- Ultra lightweight shell made with Polycarbonate / ABS material provides superior protection
- Mips® (Multi-directional Impact Protection System) is a low frictional layer designed to reduce rotational motion transferred to the head from angled impacts
- EPS foam impact liner helps absorb the forces of front, side, or rear impacts
- Includes a 4-point cross-over chin strap with quick release buckle that is adjustable for a safe & secure fit
- Rugged non-slip adjustable SURE-LOCK wheel ratchet ensures proper suspension performance and effortless fit for all head sizes
- Inner suspension includes comfortable padding for above the brow line

Technical Data

Color	White, Black, Yellow, Orange, Red, Hi-Vis Yellow
Sizes Available	OS
Packaging	Boxed
Packed	18/Case
Case Dimensions (in)	28.35 x 11.61 x 30.71
Case Weight (lbs)	24.69
Country of Origin	China
Shell Material	ABS / Polycarbonate
Shell	Vented
Brim Style	Cap Style
Brim Length	Micro
Size Adjustment	Wheel Ratchet
Suspension	--
Chin Strap	4-Point Polyester
Sweatband	--
Construction	MIPS Technology
Certifications	EN 397, EN 12492
Product Circularity	--

Performance Data

ANSI Type	Type II
CSA Type	--
Electrical Class	C

Care Instructions

The unit may be cleaned with soap and warm water and dried with a soft cloth. The helmet should not be cleaned with chemical or abrasive cleaners. The helmet should be stored out of direct sunlight, away from chemicals and not exposed to extremes of temperature.



SPECIFICATION SHEET

STYLE: 280-HP1491RVM

SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
280-HP1491RVM-11	Black	OS	616314731372	10616314731379	20616314731376
280-HP1491RVM-44	Hi-Vis Yellow	OS	616314731396	10616314731393	20616314731390
280-HP1491RVM-03	Orange	OS	616314731419	10616314731416	20616314731413
280-HP1491RVM-15	Red	OS	616314731433	10616314731430	20616314731437
280-HP1491RVM-01	White	OS	616314731457	10616314731454	20616314731451
280-HP1491RVM-02	Yellow	OS	616314731471	10616314731478	20616314731475

PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: +1 (800) 262-5755 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED. 2022-12-05