



# kramer

## C-USB/C

USB 2.0 Type-C Cable

---



Kramer's C-USB/C cables connect USB-C enabled devices with standard USB-A, B and Micro B devices (laptops, hard drives, legacy printers, hubs, smartphones, tablets and cameras). C-USB/C cables offer a whole new level of connectivity to devices using the new USB Type-C connector.

The symmetrical, low profile USB Type-C connector can be plugged in any direction, eliminating the frustration of getting the port insertion just right

## FEATURES

---

**Quality Construction** - High-quality shielded twisted pair (STP) construction, helps to prevent electromagnetic interference and ensures reliable data communication

**Reversible USB Type-C Connector**

**Max. Data Rate** - 480Mbps

**Current Rating** - 3A and 5A

**PC, Mac & Mobile Compatible**

**Plug and Play** - For printers, scanners, keyboards and other digital devices

**Backward Compatibility** - USB specifications 1.0 and 1.1

**Molded Strain Relief** - On the USB A, B & Micro B ends

**RoHS Compliant**



# kramer

## TECHNICAL SPECIFICATIONS

---

ELECTRICAL	TYPE: USB 2.0
	MAX. DATA RATE: 480Mbps
	POWER RATING: 100W max
PHYSICAL	CONNECTOR A: USB Type-C male
	CONNECTOR B: C-USB/CC - USB Type-C male
	C-USB/CB - USB Type-B male
	C-USB/CA - USB Type-A male
	C-USB/CMicroB - USB Type-Micro B male
	CONNECTOR PLATING: Nickel
	CONDUCTORS: 28AWG
	CABLE SHIELD TYPE: Aluminum-Mylar foil with braid
	OVERALL SHEATH DIAMETER: 4.0mm
	OUTER SHEATH COLOR: White
STANDARDS COMPLIANCE	REGULATORY: RoHS 2011/65/EU



# kramer

## CONFIGURATIONS

---

C-USB/CC-6	USB 2.0 USB-C(M) to USB-C(M)
------------	------------------------------

---

C-USB/CC-10	USB 2.0 USB-C(M) to USB-C(M)
-------------	------------------------------

---

C-USB/CB-6	USB 2.0 USB-C(M) to USB-B(M)
------------	------------------------------

---

C-USB/CB-10	USB 2.0 USB-C(M) to USB-B(M)
-------------	------------------------------

---

C-USB/CA-6	USB 2.0 USB-C(M) to USB-A(M)
------------	------------------------------

---

C-USB/CA-10	USB 2.0 USB-C(M) to USB-A(M)
-------------	------------------------------

---

C-USB/CMicroB-3	USB 2.0 USB-C(M) to USB Micro-B(M)
-----------------	------------------------------------

---

C-USB/CMicroB-6	USB 2.0 USB-C(M) to USB Micro-B(M)
-----------------	------------------------------------

---