

# Product data sheet

Specifications

## APC Smart-UPS SRT 48V 1kVA 1.5kVA RM Battery Pack



SRT48RMBP


### Overview

Lead time Usually in Stock

### Main

Product or Component Type	Battery
Number of rack unit	2U
Battery Type	Lead-Acid battery
Provided Equipment	Documentation CD Installation guide Rack Mounting brackets Warranty card
Range of Product	Smart-UPS Battery Systems

### Batteries & Runtime

Battery Slots Empty	0
Included Battery Modules	0
Device mounting	Stand alone battery stack
Battery Voltage	48V
RBC Quantity	2
Replacement battery	<a href="#">APCRBC155</a> 

### Physical

Color	Black
Height	3.3 in (85 mm)
Width	17.008 in (432 mm)
Depth	21.1 in (536 mm)
Net Weight	65.9 lb(US) (29.9 kg)
Mounting Mode	Rack-mounted

### Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Operating altitude	0...10000 ft
Relative Humidity	0...95 % non-condensing
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)

---

<b>Storage altitude</b>	0...50000 ft (0...15240 m)
-------------------------	----------------------------

---

<b>Storage Relative Humidity</b>	0...95 % non-condensing
----------------------------------	-------------------------

---

## Ordering and shipping details

---

<b>Category</b>	80230-IG SEBA TO SEUSA
-----------------	------------------------

---

<b>Discount Schedule</b>	BMS1
--------------------------	------

---

<b>GTIN</b>	731304330103
-------------	--------------

---

<b>Returnability</b>	No
----------------------	----

---

<b>Country of origin</b>	PH
--------------------------	----

---

## Packing Units

---

<b>Unit Type of Package 1</b>	PCE
-------------------------------	-----

---

<b>Nbr. of units in pkg.</b>	1
------------------------------	---

---

<b>Package 1 Height</b>	9.6 in (24.5 cm)
-------------------------	------------------

---

<b>Package 1 Width</b>	27.2 in (69.0 cm)
------------------------	-------------------

---

<b>Package 1 Length</b>	23.4 in (59.5 cm)
-------------------------	-------------------

---

<b>Package weight(Lbs)</b>	71.83 lb(US) (32.58 kg)
----------------------------	-------------------------

---

## Contractual warranty

---

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

---



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

### Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

No

[EU RoHS Directive](#)

Compliant with Exemptions

SCIP Number

409c68a1-39a6-4e5f-b080-12befe783ad8

REACH Regulation

[REACH Declaration](#)

California proposition 65

**WARNING:** This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

### Energy efficiency

Optimized Energy Efficiency

Energy efficient product

## Use Again

### Repack and remanufacture

Circularity Profile

[End of Life Information](#)

Removable battery

User replaceable

Take-back

Yes

WEEE Label


 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

---

