



# Part Number: 10GX KEYCONNECT JACKS

10GX Modular Jack, Category 6A, RJ45, KeyConnect Style

# **Product Description**

CAT6A KeyConnect Jacks are available in several colors.

# **Technical Specifications**

## **Product Overview**

Environmental Space:	Indoor
Suitable Applications:	IBDN System 10GX, TIA Category 6A, ISO Class EA, 10GBASE-T

# **Physical Characteristics (Overall)**

Height:	0.9 in
Width:	0.675 in
Depth:	1.17 in
Wiring Scheme:	T568A/B
Packaging:	Individually packaged in a plastic bag. Standard pack of 50 units.
Weight:	0.016 lbs

# **Connectors**

## Materials

Description	Material	Туре
Front Connection	Flexible PCB with 50 $\mu$ inch Gold over Nickel	Flexible PCB
Rear Connection	Phosphor Bronze with Tin Plating over Nickel	IDC
Connector Body	Plastic - UL94V-0	

## **Electrical Characteristics**

Dielectric Strength:	1,000V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm
Termination Resistance:	2.5 mOhm

# **Temperature Range**

Installation Temp Range:	-10°C to +60°C
Storage Temp Range:	-40°C to +70°C
Operating Temp Range:	-10°C to +60°C

#### **Mechanical Characteristics**

Footprint/Type:	KeyConnect
Tool Compatibility:	Belden 110 Connecting Tool
Plug /Jack Compatibility:	RJ45, RJ11
Termination Front Connection:	Mated Connection
Termination Front Connection Durability:	750 cycles
Termination Rear Connection:	IDC Connection

Termination Rear Connection Durability:	20 terminations
Cable/Connector Retention:	15 lbs.
Connector/Hardware Retention:	20 lbs
Plug/Connector Retention:	11.250 lbs

#### **Standards**

Data Category:	Category 6A
Telecommunications Standards:	ISO/IEC 11801:2002 Amendment 2
Other Standards:	FCC Part 68, Subpart F, IEC 60603-7
Third Party Performance Verification:	ETL - Verified Category 6A

## **Applicable Environmental and Other Programs**

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-07-01
MII Order #39 (China RoHS):	EUP 50

## Flammability, LS0H, Toxicity Testing

Safety Listing:	ACA, c(UL)us Listed

#### **Part Number**

Related Parts: Compatible with KeyConnect Faceplates, Adapters, Boxes and Patch Panels

#### Variants

Item #	Color	Packaging	Wiring Scheme
AX102281	Almond	Single Pack	T568A/B
AX102283	Black	Single Pack	T568A/B
AX104156	Blue	Single Pack	T568A/B
AX104158	Brown	Single Pack	T568A/B
AX102282	Electric White	Single Pack	T568A/B
AX102280	Gray	Single Pack	T568A/B
AX104155	Green	Single Pack	T568A/B
AX103073	Ivory	Single Pack	T568A/B
AX104152	Orange	Single Pack	T568A/B
AX104157	Purple	Single Pack	T568A/B
AX102288	TIA Blue	Single Pack	T568A/B
AX102290	TIA Brown	Single Pack	T568A/B
AX102287	TIA Green	Single Pack	T568A/B
AX102284	TIA Orange	Single Pack	T568A/B
AX102289	TIA Purple	Single Pack	T568A/B
AX102285	TIA Red	Single Pack	T568A/B
AX102286	TIA Yellow	Single Pack	T568A/B
AX104154	Yellow	Single Pack	T568A/B

#### **Product Notes**

Included Parts:	1 X-Bar
Notes:	Please see Installation Guide PX103771

#### © 2019 Belden, Inc

#### All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.