

## 10W Wireless Fast-Charging Pad, Black

MODEL NUMBER: U280-Q01FL-BK



Qi wireless phone charger transfers battery power to your device without connecting a troublesome cable between them.

### Features

**Wireless Cell Phone Charger Delivers up to 10W for Apple and Samsung Phones** Who wants to plug and unplug power cords when you just want to charge your cell phone? The U280-Q01FL-BK makes charging more convenient by doing it wirelessly. Just place your Qi-certified device on the round charging pad. That's all there is to it. This wireless phone charger even works through most protective phone cases up to 5 millimeters. **Note:** please remove any magnetic or metal objects from your phone or case before charging.

**Compatible with Qi-Certified Cell Phones to Ensure a Safe, Flawless Charge** The U280-Q01FL-BK works with all Qi smartphones from Apple, Sony, LG, Samsung, Nokia and other popular brands. It protects your expensive device from overheating and overcharging that could lead to internal damage. An LED glows blue to indicate the charging process is underway and changes to red to let you know your phone is at 100%. The portable lightweight pad is just four inches in diameter, so it fits easily on your desktop or bedside table. An included USB cable connects the charger to a user-supplied QC USB wall charger or power adapter (QC 2.0 or 3.0 adapter is recommended for high-speed charging).

### Highlights

- Charges your Apple iPhone, Google Pixel or Samsung Galaxy wirelessly without a cable
- LED glows blue during charging and turns red to indicate device is fully charged
- Charges your smartphone through its protective case to avoid the hassle of removing it
- Prevents overheating and overcharging to protect your essential device from damage
- Universally compatible with all Qi-certified smartphones and other devices

### Applications

- Transfer power from a wall charger or power adapter to your smartphone's battery without the burden of carrying and connecting extra cabling

### System Requirements

- Compatible with all Qi-certified smartphones, including the latest Apple iPhone, Google Pixel and Samsung Galaxy devices

### Package Includes

- U280-Q01FL-BK Wireless Charging Pad, Black
- USB 2.0 A to Micro-B cable, 3 ft.
- Quick Start Guide

## Specifications



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

OVERVIEW	
UPC Code	037332247070
Product Type	Wireless Charger
Charging Form Factor	Pad/Stand
Device Compatibility	Phone; Tablet; Amazon Kindle; Headphones; Watch
Technology	USB
INPUT	
Nominal Input Voltage(s) Supported	9V DC
Input Plug Type	USB MICRO-B (FEMALE)
OUTPUT	
Output Capacity	5V/1A (5W); 9V/1.1A (10W)
Overload Protection	Yes
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red (Power, Fully Charged); Blue (Charging)
CHARGING	
Number of Charging Ports	0
Total Charging Amps	1.1A
Total Charging Watts	10
Charging Method	Wireless
Charging Port Type	WIRELESS CHARGING COIL
Charging Ports Details	5V/1A (5W); 9V/1.1A (10W)
Charging Ports / Amps	1A
Charging Method Detail	Qi Compatible; Quick Charge 3.0; Quick Charge 2.0
PHYSICAL	
Color	Black
Unit Dimensions (hwd / in.)	4.12 x 4.12 x 0.50
Unit Packaging Type	Box
Unit Weight (kg)	0.20
Unit Weight (lbs.)	0.44
ENVIRONMENTAL	
Operating Temperature Range	32 to 95°F (0 to 35°C)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Storage Temperature Range	-4 to 158°F (-20 to 70°C)
Operating Humidity Range	10% to 80% RH, Non-Condensing
Storage Humidity Range	5% to 95% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	MICRO-USB B (FEMALE)
Side B - Connector 1	WIRELESS CHARGING COIL
<b>FEATURES &amp; SPECIFICATIONS</b>	
Driver Required	No
<b>SPECIAL FEATURES</b>	
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>