

Side panel, screw-fastened, sheet steel

for VX, VX IT

- Time-saving assembly thanks to clip-in side panel holders
- Automatic potential equalisation and higher EMC protection, thanks to enclosure panel holders with earthing inserts located on the inside
- Easy positioning in the height and depth with the location aid
- Simple assembly
- Earthing bolts with large, paint-free contact surface for optimum contact

Material:

- Sheet steel, 1.5 mm

Surface finish:

- Dipcoat-primed, powder-coated on the outside

Colour:

- RAL 7035

Protection category IP to IEC 60 529:

- IP 55 (in conjunction with enclosures from the VX, VX IT series)

Protection category NEMA:

- NEMA 12 (in conjunction with enclosures from the VX, VX IT series)

Supply includes:

- Assembly parts

For enclosures		Packs of	Model No.
Height mm	Depth mm		
800	600	2 pc(s).	8173.245
1200	500	2 pc(s).	8115.245
1200	600	2 pc(s).	8170.245
1200	800	2 pc(s).	8175.245
1200	1000	2 pc(s).	8176.245
1400	500	2 pc(s).	8145.245
1600	500	2 pc(s).	8165.245
1600	600	2 pc(s).	8166.245
1600	800	2 pc(s).	8168.245
1800	400	2 pc(s).	8184.245
1800	500	2 pc(s).	8185.245
1800	600	2 pc(s).	8186.245
1800	800	2 pc(s).	8188.245
2000	400	2 pc(s).	8104.245
2000	500	2 pc(s).	8105.245
2000	600	2 pc(s).	8106.245
2000	800	2 pc(s).	8108.245
2000	1000	2 pc(s).	8100.245
2000	1200	2 pc(s).	8102.245
2200	600	2 pc(s).	8126.245
2200	800	2 pc(s).	8128.245
2200	1000	2 pc(s).	8120.245
2200	1200	2 pc(s).	8122.245



Accessories:

- Hinge for side panel, screw-fastened, sheet steel, see page 902



Side panel, screw-fastened, stainless steel

for VX

- Time-saving assembly thanks to clip-in side panel holders
- Automatic potential equalisation and higher EMC protection, thanks to enclosure panel holders with earthing inserts located on the inside
- Easy positioning in the height and depth with the location aid
- Simple assembly
- Earthing bolts with large, paint-free contact surface for optimum contact

Material:

- Stainless steel 1.4301 (AISI 304), 1.5 mm

Surface finish:

- Brushed, grain size 400

Protection category IP to IEC 60 529:

- IP 55 (in conjunction with enclosures from the VX series)

Protection category NEMA:

- NEMA 12 (in conjunction with enclosures from the VX series)

Supply includes:

- Assembly parts

For enclosures		Packs of	Model No.
Height mm	Depth mm		
1800	400	2 pc(s).	8700.030
1800	500	2 pc(s).	8700.040
2000	600	2 pc(s).	8700.050

