

APC AR3150 rack cabinet 42U Freestanding rack Black

Brand : APC

Product code: AR3150

Product name : AR3150

NetShelter SX 42U 750mm Wide x 1070mm Deep Enclosure with Sides Black

[APC AR3150 rack cabinet 42U Freestanding rack Black:](#)

Rack enclosures with advanced cooling, power distribution, and cable management for server and networking applications in IT environments.

Includes: Casters, Doors, Ground Studs, Installation Guide, Leveling feet, Mounting Hardware, Roof, Side Panels

APC AR3150. Type: Freestanding rack, Rack capacity: 42U, Maximum weight capacity: 1704 kg. Weight: 155.9 kg. Product colour: Black



Features		Weight & dimensions	
Rack capacity *	42U	Weight	155.9 kg
Type *	Freestanding rack	Mounting depth (min)	26.2 cm
Maximum weight capacity *	1704 kg	Mounting depth (max)	91.5 cm
Product colour	Black	Packaging data	
Weight & dimensions		Package weight	168.2 kg
Size (imperial)	48.3 cm (19")	Other features	
Width	750 mm	Dimensions (WxDxH)	750 x 1070 x 1991 mm
Depth	1070 mm	Package dimensions (WxDxH)	895 x 1219 x 2216 mm
Height	1991 mm	Dynamic load	1022.73 kg
		Static load	1363.64 kg



731304236375

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 01-MAR-2022. Prints or copies of Information are only valid on the printed Publication date