

# **ARD-EntryProx - with keypad**



The ARD-EntryProx access control terminal allows self-sufficient access with a card and/or PIN code. It can control a door. It is possible to connect it to an access controller via the Wiegand interface.

## **Installation/Configuration Notes**

- Four Wiegand interfaces for connecting readers.
- Up to four readers can be installed per entrance. Please follow the general mounting instructions for the proximity reader regarding the distance between readers and metallic surfaces.

- Compact access terminal (surface-mounted) with reader unit for proximity cards and keypad for PIN code entry and configuration
- ► Self-sufficient operation
- Transaction memory for a maximum of 1000 transactions; transaction consists of personal ID, time, date and type of transaction
- ► Maximum of 2000 personal IDs
- Configurable PIN code block after a specified number of incorrect entries
- Quick personal activation by showing card
- ► Alarm via auxiliary relay

#### **Parts Included**

## **Quantity Component**

- 1 Keypad/unit housing
- 1 Housing rear panel
- 4 Connection cable
- 1 Rear panel for antenna module
- 1 Antenna housing
- 1 Cover for antenna shaft
- 1 Jumper
- 4 One-sided adhesive rubber feet
- 4 Screws
- 1 Installation guide

#### **Technical Specifications**

# Housing

External dimensions (W x H x D) 133 x 70 x 35 mm

Material Polycarbonate (UL 94)

Color Black Weight 158 g

**Connections** 

Display 3 LEDs
Beeper 4 kHz
Interfaces Wiegand

## 2 | ARD-EntryProx - with keypad

#### Housing

#### **Environmental conditions**

Operating temperature -30° to +65°C

Humidity 10 to 95% no condensation water **Environment class** IP 50 (when installed in damp or wet

environment, a weather-proof hous-

ing is necessary)

**Electrical parameters** 

Power supply 10 to 15 VDC Current consumption 150 mA

Note: Power supply e.g. with 12 V power supply unit plug, 500 mA Mat. no. 4.998.118.694

HID - PROX Reading process Operating/modulation frequency 125 kHz

Reading distance 4 to 6 cm with ISO card

Relay

Max. 4 A DC Main relay Auxiliary relay Max. 1 A DC

## **Ordering Information**

ARD-EntryProx - with keypad

**ARD-ENTRYPROX** 

Compact access reader with keypad.

Americas:
Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180 security.sales@us.bosch.com www.boschsecurity.us

Europe, Middle East, Africa: Bosch Security Systems B.V. P.O. Box 80002

5600 JB Eindhoven, The Netherlands Phone: +31 40 2577 284 Fax: +31 40 2577 330 emea.securitysystems@bosch.com www.boschsecurity.com

Asia-Pacific: Repr Robert Bosch (SEA) Pte Ltd, Security Systems 11 Bishan Street 21 Singapore 573943 Phone: 465 6258 5511 Fax: 465 6571 2698 Represented by apr.securitysystems@bosch.com www.boschsecurity.com