

Product datasheet

Specifications



APC Replacement Battery Cartridge for Smart-UPS On-Line, 12V 5Ah lead-acid battery, 2-year repair or replace warranty

APCRBC152

Overview

Lead time Usually in Stock

Main

Product or component type Replacement battery cartridge
Battery type Lead-acid battery
Provided equipment Installation guide
Range of product Replacement Battery Cartridges

Batteries & Runtime

Number of battery free slots 0
Number of battery filled slots 0
Device mounting Enclosed battery cartridge
Number of battery replacement quantity 1

Physical

Colour Black
Height 76 mm
Width 210 mm
Depth 762 mm
Net weight 15.29 kg
Mounting mode Not rack-mountable

Environmental

Ambient air temperature for operation 0...40 °C
Operating altitude 0...10000 ft
Relative humidity 0...95 % non-condensing
Ambient air temperature for storage -15...45 °C
Storage altitude 0...15240 m
Storage Relative Humidity 0...95 % non-condensing

Packing Units

Unit Type of Package 1 PCE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number of Units in Package 1	1
Package 1 Height	19.000 cm
Package 1 Width	35.000 cm
Package 1 Length	64.000 cm
Package 1 Weight	18.460 kg
Unit Type of Package 2	P06
Number of Units in Package 2	4
Package 2 Height	75.000 cm
Package 2 Width	80.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	81.840 kg

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint	57
----------------------------------	----

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
--	-----

Packaging without single use plastic	No
--------------------------------------	----

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
-----------------------------------	--

SCIP Number	25764278-9ac2-4c03-941a-d133167ad10f
-------------	--------------------------------------

REACH Regulation	REACH Declaration
------------------	-----------------------------------

Halogen-free status	Product contains halogen above thresholds
---------------------	---

Use Again

Repack and remanufacture

End of life manual availability	End of Life Information
---------------------------------	---

Take-back	No
-----------	----


WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
------------	---

Image of product / Alternate images

Alternative

