



Part Number: MEDIAFLEX RCA INSERT

RCA Insert for MediaFlex, 3-Port

Product Description

MediaFlex RCA Insert, 3-Port, Available in several colors.

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	Multimedia

Physical Characteristics (Overall)

Height:	1.39 m
Width:	2.05
Depth:	1.41
Packaging:	Individually packaged in a plastic bag.
Weight:	0.05 kg

Connectors

Materials

Description	Material	Type
Front Connection	Metal	RCA
Rear Connection	Plastic - UL94V-0	110
Insert	Plastic - UL94V-0	

Temperature Range

Installation Temp Range:	-10 to 60°C
Storage Temp Range:	-40 to 70°C
Operating Temp Range:	-10 to 60°C

Mechanical Characteristics

Footprint/Type:	Mediaflex
Tool Compatibility:	Termination Station (AX101852), Release Tool (AX101185)

Applicable Environmental and Other Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-01-07
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	ACA, Bi-national Standard Listed
-----------------	----------------------------------

Part Number

Related Parts:	Compatible with MediaFlex Faceplates
----------------	--------------------------------------

Variants

Item #	Color
AX101878	Almond
AX101880	Black
AX101877	Gray
AX102578	Ivory
AX101879	White
AX102616	White

Product Notes

Included Parts:	Pin assignement guide
Notes:	For proper installation refer to Installation Guide PX102063 available on our web site at http://www.belden.com

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.