



netSELECT™

Structured Cabling Network Enclosures

Control Home Automation Systems.

Share Single Analog, Cable or DSL Internet Connection.

Multiple Telephone Distribution; Call Handling (PBX).

Video Distribution.



FEATURES

- Local file access.
- Shared peripherals.
- Play games that allow multi-users.

STANDARDS/VERIFICATIONS

System Enclosure:

- ◆ Material: 18 gauge steel.
- ◆ Finish: white, powder coat.
- ◆ UL and cULus Listed 1863.

Network Modules:

- ◆ Meets FCC Part 68 standard.
- ◆ Finish: black, powder coat.
- ◆ UL and cULus Listed 1863.

netSELECT™ is an innovative network solution that's perfect for any home or small office. Specifically positioned as the voice/data segment for the **homeSELECT™** brand, the **netSELECT™** System satisfies the need for a dependable, flexible system that can accommodate all of today's fast-changing voice, data and video requirements. This cost-effective solution incorporates all the quality you'd expect from Hubbell. Built-in flexibility makes it easy to upgrade and keep pace with evolving technologies.

EASY FOR INSTALLERS


An easy-to-hang cabinet featuring surface or recess mounts between 16" studs on center, 2"x 4" minimum. **netSELECT™** Modular Components snap into the box horizontally or vertically, optimizing space. A blank module provides flexibility for installers to use their own choice of manufacturer's active components. Also included: A reversible and lockable hinged door, ample cable entrance locations and a complete offering of jacks, plates and other work station accessories.

EASY FOR USERS

Built in flexibility to upgrade and keep pace with evolving technologies. An easy-to-read label helps you to keep track of the system's infrastructure. The white powder coat finish provides a clean, durable chassis to house all components.

Advantages and Wiring Layout

*Tomorrow's Communications Entail A Lot More Than Just Talking.
netSELECT™ Keeps You Wired To Everything.*



netSELECT™ Structured Cabling Network Enclosures

FEATURES

- Flush or surface mount enclosure (hardware provided).
- Hinged cover can be mounted to swing from either side.
- Integral trim ring hides rough-in hole in sheet rock providing a finished appearance.
- Horizontal and vertical module mounting holes for maximum density.
- Unique 89D bracket mounting holes allow easy mounting of 66 blocks and peripherals.
- Provisions to mount optional duplex power and lock kit available.
- Integral cable management slots and tie-wraps provided to help dress cable runs.
- Additional nylon push pins provided to assist module mounting.

SPECIFICATIONS

- ◆ Material: 18 gauge steel.
- ◆ Finish: white, powder coat.
- ◆ UL and cULus Listed 1863.

Order Information

netSELECT™ Pre-configured Network System

Catalog No.

Basic home network kit includes:

- 1 box with hinged cover (NSOBOX14)
- 1 primary 8-port telephone module (NSOPTM8)
- 1 4-way coax splitter module (NSOVD4)

NSOBNK14



Structured Media Enclosure with Hinged Cover, 14"

Catalog No.

Dimensions: 14.38"W x 14"H x 3.96"D

Knockouts:

- Top: two 1½" and three 1½" or 2" combo;
- Bottom: one 1½" and one 1½" or 2" combo;
- Back: two 1¼"

NSOBOX14



Structured Media Enclosure with Hinged Cover, 28"

Catalog No.

Dimensions: 14.38"W x 28"H x 3.96"D

Knockouts:

- Top: five 2";
- Bottom: five 2", two power kit knockouts;
- Back: eight 1¼"

NSOBOX28



Structured Media Enclosure with Hinged Cover, 48"

Catalog No.

Dimensions: 14.38"W x 48"H x 3.96"D

Knockouts:

- Top: five 2";
- Bottom: two power kit knockouts;
- Back: none

NSOBOX48

netSELECT™ Network Modules

netSELECT™ Modular Components enable the designer to select performance requirements specifically for the application. Modules snap horizontally or vertically into the enclosures for maximum flexibility and optimum space usage.

SPECIFICATIONS

- ◆ Dimensions: 6.47"W x 2.95"H, except NSOMTM24: 6.47"H x 6"H.
- ◆ Meets FCC Part 68 standard.
- ◆ Finish: black powder coat.
- ◆ UL and cULus Listed 1863.



ORDER INFORMATION

Primary Telephone Module, 8-port



Catalog No. **NSOPTM8**
 Supports 8 phone outlets with up to 4 incoming lines for voice, fax or modem applications in a protected PCB module. Pre-mounted push pins snap the module quickly into place. RJ31X interface jack included for security system connection. RJ45 jack interfaces with optional NSOETM8 Telephone Expansion module for additional extensions.

Data Module, 8-port



Catalog No. **NSODM8**
 Category 5e **NSODM8**
 Category 6 **NSODM8C6**
 Supports Gigabit Ethernet for up to 8 data lines with front 110 punch down terminations in a protected PCB module. Pre-mounted push pins snap the module quickly into place.

Expansion Telephone Module, 8-port



Catalog No. **NSOETM8**
 Adds an additional 8 phone outlets with up to 4 incoming lines when used with the primary telephone module. Pre-mounted push pins snap the module quickly into place. Includes RJ45 jumper cord to connect with NSOPTM8 Primary Telephone module.

Combination Module



Catalog No. **NSO6P1DM**
 6-Port Telephone and 1-Port Data
 Provides basic telephone and data delivery in a small package. Allows data lines to be converted to voice, with the move of a patch cord.

Telephone Module, Multiport Patchable



Catalog No. **NSOMTM24**
 Terminates lines via modular plug to accommodate flexibility, by changing plug locations. Allows data lines to be converted to voice, with the move of a patch cord. Includes nine RJ45 jumper cords.

Blank Module Plate



Catalog No. **NSOBM**
 Module allows mounting of active components (i.e. switches, routers) or other devices (66 blocks, audio components) onto a modular platform. Can be custom drilled or used with two self-adhesive VELCRO® strips included to mount components onto module. Pre-mounted push pins snap the module quickly into place.

Please see the netSELECT™ Catalog or Hubbell Premise Wiring's website for more netSELECT™ products and accessories.

VELCRO® is a registered trademark of Velcro Industries B.V.



Hubbell Premise Wiring

HUBBELL INCORPORATED (Delaware)
 14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005
 Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

Worldwide Locations

Hubbell Premise Wiring, Asia Pacific
 Hubbell Canada Inc.
 Hubbell Premise Wiring, Central America
 Hubbell Premise Wiring, China
 Hubbell Premise Wiring, Colombia
 Hubbell Premise Wiring, Europe
 Hubbell Int'l. Inc., Korea Branch

852-2836-7131 Fax: 852-2836-7132
 905-839-1138 Fax: 905-839-9108
 506-309-4158 Fax: 506-260-1616
 86-21-6374 2660 Fax: 86-21-6374 2799
 571-245-8940 Fax: 571-340-0925
 44-01283 500500 Fax: 44-01283 500400
 (82 2) 2607 1363 Fax: (82 2) 2603 7386

Hubbell Premise Wiring, Latin America
 Hubbell de Mexico, S.A. de C.V.
 Hubbell Premise Wiring, Middle East
 Hubbell-Taian Co., Ltd., Taiwan
 Hubbell Premise Wiring, Turkey
 Hubbell Premise Wiring, Venezuela

305-408-4501 Fax: 305-408-8201
 (5255) 9151-9999 Fax: (5255) 9151-9989
 971-4-393-4192 Fax: 971-4-393-4194
 886-2-2522-1862 Fax: 886-2-2522-1872
 90-216-313-5016 Fax: 90-216-414-8148
 58-416-680-7453 Fax: 58-281-274-7900