



Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 6

TEROSON MS 9399 BK known as TEROSTAT MS 9399 SW KK
400 ML

sds no. : SET000624801
V002.3
Revision: 10.01.2013
printing date: 05.11.2013

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

TEROSON MS 9399 BK known as TEROSTAT MS 9399 SW KK 400 ML

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Part B of a two part adhesive

1.3. Details of the supplier of the safety data sheet

Henkel Limited

Apollo Court, 2 Bishop Square Business Park

AL10 9EY Hatfield

Great Britain

Phone: +44 (1707) 635000

Fax-no.: +44 (1707) 635099

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

No data available.

Classification (DPD):

The product is not subject to classification according to the calculation methods of the "General Classification Guideline for Preparations of the EC" as issued in the last version.

2.2. Label elements

Label elements (CLP):

No data available.

Label elements (DPD):

No classification required.

2.3. Other hazards

None if used properly.

SECTION 3: Composition/information on ingredients

General chemical description:

Adhesive

Base substances of preparation:

Polymer, silan- terminated

Declaration of the ingredients according to CLP (EC) No 1272/2008:

No data available.

Declaration of ingredients according to DPD (EC) No 1999/45:

Contains no dangerous substances exceeding the limits of the EU-Regulation

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

All common extinguishing agents are suitable.

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In case of fire toxic gases can be released.

5.3. Advice for firefighters

Wear protective equipment.

Wear self-contained breathing apparatus.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Remove mechanically.

Dispose of contaminated material as waste according to Chapter 13.

6.4. Reference to other sections

See advice in chapter 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Hygiene measures:

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

Ensure good ventilation/extraction.

Store frost-free.

Storage at 15 to 25°C is recommended.

7.3. Specific end use(s)

Part B of a two part adhesive

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for

Great Britain

None

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Suitable breathing mask when there is inadequate ventilation.

Hand protection:

Chemical-resistant protective gloves (EN 374). Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374): Polychloroprene (CR; ≥ 1 mm thickness) or natural rubber (NR; ≥ 1 mm thickness) Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374): Polychloroprene (CR; ≥ 1 mm thickness) or natural rubber (NR; ≥ 1 mm thickness) This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Protective goggles

Skin protection:
Wear protective equipment.

Advices to personal protection equipment:
Use only personal protection that's CE-labelled according to the regulation no. 819 of 19 August 1994.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

| | |
|---|------------------------------------|
| Appearance | paste pasty black |
| Odor | characteristic |
| Odour threshold | No data available / Not applicable |
| pH | No data available / Not applicable |
| Initial boiling point | No data available / Not applicable |
| Flash point | > 93,00 °C (> 199,4 °F) |
| Decomposition temperature | No data available / Not applicable |
| Vapour pressure | No data available / Not applicable |
| Density (20 °C (68 °F)) | 1,38 g/cm ³ |
| Bulk density | No data available / Not applicable |
| Viscosity (Physica Rheolab; 20 °C (68 °F)) | 120 pa.s |
| Viscosity (kinematic) | No data available / Not applicable |
| Explosive properties | No data available / Not applicable |
| Solubility (qualitative) (20 °C (68 °F); Solvent: Water) | Insoluble |
| Solidification temperature | No data available / Not applicable |
| Melting point | No data available / Not applicable |
| Flammability | No data available / Not applicable |
| Auto-ignition temperature | No data available / Not applicable |
| Explosive limits | No data available / Not applicable |
| Partition coefficient: n-octanol/water | No data available / Not applicable |
| Evaporation rate | No data available / Not applicable |
| Vapor density | No data available / Not applicable |
| Solid content | 97 % |
| Oxidising properties | No data available / Not applicable |

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

None if used for intended purpose.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None known if used to the intended purpose.

10.5. Incompatible materials

None if used properly.

10.6. Hazardous decomposition products

No decomposition if used according to specifications.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General toxicological information:

To the best of our knowledge no harmful effects are to be expected if the product is handled and used properly.

SECTION 12: Ecological information

General ecological information:

Do not empty into drains, soil or bodies of water.

12.1. Toxicity

No data available.

12.2. Persistence and degradability

No data available.

12.3. Bioaccumulative potential / 12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

The valid EEC waste code numbers are not product-related but are largely source-related. These can be requested from the manufacturer.

In consultation with the responsible local authority, must be subjected to special treatment.

SECTION 14: Transport information

- 14.1. UN number**
Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**
Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**
Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.
- 14.4. Packaging group**
Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.
- 14.5. Environmental hazards**
Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.
- 14.6. Special precautions for user**
Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.
- 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code**
not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content 0 %
(VOCV 814.018 VOC regulation
CH)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.



Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 6

TEROSON MS 9399 BK known as TEROSTAT MS 9399 SW KK
400 ML

sds no. : 111912
V002.3

Revision: 10.01.2013
printing date: 05.11.2013

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

TEROSON MS 9399 BK known as TEROSTAT MS 9399 SW KK 400 ML

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Adhesive

1.3. Details of the supplier of the safety data sheet

Henkel Limited
Apollo Court, 2 Bishop Square Business Park
AL10 9EY Hatfield

Great Britain

Phone: +44 (1707) 635000
Fax-no.: +44 (1707) 635099

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

No data available.

Classification (DPD):

The product is not subject to classification according to the calculation methods of the "General Classification Guideline for Preparations of the EC" as issued in the last version.

2.2. Label elements

Label elements (CLP):

No data available.

Label elements (DPD):

No classification required.

2.3. Other hazards

None if used properly.

SECTION 3: Composition/information on ingredients

General chemical description:

Adhesive

Base substances of preparation:

Polymer, silan- terminated

Declaration of the ingredients according to CLP (EC) No 1272/2008:

No data available.

Declaration of ingredients according to DPD (EC) No 1999/45:

Contains no dangerous substances exceeding the limits of the EU-Regulation

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

All common extinguishing agents are suitable.

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In case of fire toxic gases can be released.

5.3. Advice for firefighters

Wear protective equipment.

Wear self-contained breathing apparatus.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Remove mechanically.

Dispose of contaminated material as waste according to Chapter 13.

6.4. Reference to other sections

See advice in chapter 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Hygiene measures:

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

Ensure good ventilation/extraction.

Store frost-free.

Storage at 15 to 25°C is recommended.

7.3. Specific end use(s)

Adhesive

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for

Great Britain

None

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Suitable breathing mask when there is inadequate ventilation.

Hand protection:

Chemical-resistant protective gloves (EN 374). Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374): Polychloroprene (CR; ≥ 1 mm thickness) or natural rubber (NR; ≥ 1 mm thickness) Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374): Polychloroprene (CR; ≥ 1 mm thickness) or natural rubber (NR; ≥ 1 mm thickness) This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Protective goggles

Skin protection:
Wear protective equipment.

Advices to personal protection equipment:
Use only personal protection that's CE-labelled according to the regulation no. 819 of 19 August 1994.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

| | |
|---|------------------------------------|
| Appearance | solid material pasty black |
| Odor | characteristic |
| Odour threshold | No data available / Not applicable |
| pH | No data available / Not applicable |
| Initial boiling point | No data available / Not applicable |
| Flash point | No data available / Not applicable |
| Decomposition temperature | No data available / Not applicable |
| Vapour pressure | No data available / Not applicable |
| Density (20 °C (68 °F)) | 1,35 - 1,41 g/cm ³ |
| Bulk density | No data available / Not applicable |
| Viscosity (Physica Rheolab; 20 °C (68 °F)) | 170 pa.s |
| Viscosity (kinematic) | No data available / Not applicable |
| Explosive properties | No data available / Not applicable |
| Solubility (qualitative) (20 °C (68 °F); Solvent: Water) | Insoluble |
| Solidification temperature | No data available / Not applicable |
| Melting point | No data available / Not applicable |
| Flammability | No data available / Not applicable |
| Auto-ignition temperature | No data available / Not applicable |
| Explosive limits | No data available / Not applicable |
| Partition coefficient: n-octanol/water | No data available / Not applicable |
| Evaporation rate | No data available / Not applicable |
| Vapor density | No data available / Not applicable |
| Solid content (105 °C) | 100 % |
| Oxidising properties | No data available / Not applicable |

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

None if used for intended purpose.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

None if used properly.

10.6. Hazardous decomposition products

No decomposition if used according to specifications.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General toxicological information:

To the best of our knowledge no harmful effects are to be expected if the product is handled and used properly.

SECTION 12: Ecological information

General ecological information:

Do not empty into drains, soil or bodies of water.

12.1. Toxicity

No data available.

12.2. Persistence and degradability

No data available.

12.3. Bioaccumulative potential / 12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

The valid EEC waste code numbers are not product-related but are largely source-related. These can be requested from the manufacturer.

In consultation with the responsible local authority, must be subjected to special treatment.

SECTION 14: Transport information

- 14.1. UN number**
Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**
Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**
Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.
- 14.4. Packaging group**
Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.
- 14.5. Environmental hazards**
Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.
- 14.6. Special precautions for user**
Not hazardous according to RID, ADR, ADNR, IMDG, IATA-DGR.
- 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code**
not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content 0 %
(VOCV 814.018 VOC regulation
CH)

VOC Paints and Varnishes (EU):

Product (sub)category: This product is not a subject of the Directive 2004/42/EC

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.