

Belden IBDN System 10GX

10GX Modular Cords

AX360015 10GX Modular Cord, Blue



10GX Modular Cords

The **10GX Modular Cords** are 4-pair 23 AWG UTP modular cords designed to be used within the Belden IBDN System 10GX. Belden has designed the 10GX Modular Cord based on a patent-pending management bar design which allows for very good control of the internal plug NEXT. The patch cable design offers very good Alien crosstalk performance, while maintaining the important mechanical characteristics such as flexibility. The 10GX Modular Cords' design, with a very small footprint, makes them fully compatible with the highest density hubs that utilize RJ45 jack connections. The 10GX Modular Cords are available in pantone colors that match the colors per the TIA/EIA-606 standard and the product line encompasses CMR modular cords, as well as open-ended cords. The unmatched performance exceeds all parameters specified in the proposed Augmented Category 6 standard. All performance characteristics have been set to guarantee transmission performance up to 625 MHz.

Description	Belden Part Number					
	Blue	White	Gray	Green	Red	Yellow
Belden IBDN System 10GX						
10GX Modular Cord, 4-Pair, 23 AWG Solid, T568A/B - T568A/B, CMR						
2.1 m (7 ft)	AX360015	AX360051	AX360027	AX360021	AX360045	AX360057
3.0 m (10 ft)	AX360016	AX360052	AX360028	AX360022	AX360046	AX360058
4.6 m (15 ft)	AX360017	AX360053	AX360029	AX360023	AX360047	AX360059
7.6 m (25 ft)	AX360018	AX360054	AX360030	AX360024	AX360048	AX360060
10GX Pigtail, 4-Pair, 23 AWG Solid, T568A — Open, CMR						
4.6 m (15 ft)	AX360265					
7.6 m (25 ft)	AX360266					
10.6 m (35 ft)	AX360267					
15.0 m (50 ft)	AX360268					
10GX Pigtail, 4-Pair, 23 AWG Solid, T568B — Open, CMR						
4.6 m (15 ft)	AX360269					
7.6 m (25 ft)	AX360270					
10.6 m (35 ft)	AX360271					
15.0 m (50 ft)	AX360272					

These products are in the process of being assessed for Gb/s compliance. Please check our Web Site for the most current RoHS status.