

1752A Paired - Enhanced Category 5e Bonded-Pair Cables

	<p>For more information please call 1-800-Belden1</p> <p><u>See Put-ups and Colors</u></p> <p>Related Documents : No. 8 for DataTwist Cables (Modified Western Electric).pdf</p>
--	--

Description:

24 AWG bonded-pairs stranded (7x32) TC conductors, non-plenum, Polyolefin® insulation, RJ-45 compatible, see color code chart (below), PVC jacket (red, black, yellow, green, orange, blue, purple or gray).

SUITABLE APPLICATIONS:

Suitable Applications	Premise Patch Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments
-----------------------	---

PHYSICAL CHARACTERISTICS:

CONDUCTOR:

Number of Pairs	4
Total Number of Conductors	8
AWG	24
Stranding	7x32
Conductor Material	TC - Tinned Copper

INSULATION:

Insulation Material	PO - Polyolefin
---------------------	-----------------

Pair Color Code Chart :

Number	Color	Number	Color
1	White/Blue Stripe & Blue	3	White/Green Stripe & Green
2	White/Orange Stripe & Orange	4	White/Brown Stripe & Brown

OUTER SHIELD:

Outer Shield Material	Unshielded
-----------------------	------------

OUTER JACKET:

Outer Jacket Material	PVC - Polyvinyl Chloride
-----------------------	--------------------------

OVERALL NOMINAL DIAMETER:

Overall Nominal Diameter	0.220 in.
--------------------------	-----------

MECHANICAL CHARACTERISTICS:

1752A Paired - Enhanced Category 5e Bonded-Pair Cables

Operating Temperature Range	-20°C To +80°C
Bulk Cable Weight	25 lbs/1000 ft.
Max. Recommended Pulling Tension	40 lbs.
Min. Bend Radius (Install)	0.25 in.

APPLICABLE SPECIFICATIONS AND AGENCY COMPLIANCE:

APPLICABLE STANDARDS:

NEC/(UL) Specification	CM, UL444
CEC/C(UL) Specification	CM
IEC Specification	11801 Category 5 Patch
EU CE Mark (Y/N)	Yes
EU RoHS Compliant (Y/N)	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
TIA/EIA Specification	568-B.2 Category 5e Patch
Other Specification	NEMA WC-63.1 Category 5, ICEA 661, Cat 5x-100 Patch, UL verified to Category 5e

FLAME TEST:

UL Flame Test	UL1685 UL Loading
CSA Flame Test	FT1

PLENUM/NON-PLENUM:

Plenum (Y/N)	N
--------------	---

ELECTRICAL CHARACTERISTICS:

Nom. Mutual Capacitance @ 1 KHz	15 pF/ft
Maximum Capacitance Unbalance (pF/100 m)	66 pF/100 m
Nominal Velocity of Propagation	70 %
Maximum Delay (ns/100 m)	510 ns/100 m
Maximum Delay Skew (ns/100m)	25 ns/100 m
Maximum Conductor DC Resistance @ 20 Deg. C	9 Ohms/100 m
Maximum DCR Unbalance @ 20 Deg. C	3 %
Max. Operating Voltage - UL	300 V RMS

ELECTRICAL CHARACTERISTICS - PREMISE:

Premise Cable Electricals Table 1 :

1752A Paired - Enhanced Category 5e Bonded-Pair Cables

Frequency (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min. Return Loss (dB)	Min. Structural Return Loss (dB)
1	2.4	65.3	65.3		62.9	20.0	
4	4.8	56.3	56.3		51.5	23.0	
8	6.8	51.8	51.8		45.0	24.5	
10	7.7	50.3	50.3		42.6	25.0	
16	9.7	47.3	47.3		37.5	25.0	
20	11.0	45.8	45.8		34.8	25.0	
25	12.4	44.3	44.3		31.9	24.3	
31.25	13.9	42.9	42.9		29.0	23.6	
62.5	20.2	38.4	38.4		18.3	21.5	
100	26.0	35.3	35.3		9.2	20.1	
155	33.2	32.5	32.5		0	19.0	
200	38.4	30.8	30.8			19.0	
250	43.7	29.3	29.3			18.0	
300	48.6	28.2	28.2			18.0	
310	49.5	27.9	27.9			18.0	
350	53.2	27.2	27.2			17.0	

Premise Cable Electricals Table 2 :

Frequency (MHz)	Input (Unfitted) Impedance (Ohms)	Fitted Impedance (Ohms)	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 12	105 ± 10	63.8	60.8
4	100 ± 12	100 ± 10	51.7	48.7
8	100 ± 12	100 ± 10	45.7	42.7
10	100 ± 12	100 ± 10	43.8	40.8
16	100 ± 12	100 ± 10	39.7	36.7
20	100 ± 12	100 ± 10	37.7	34.7
25	100 ± 15	100 ± 10	35.8	32.8
31.25	100 ± 15	100 ± 10	33.9	30.9
62.5	100 ± 15	100 ± 10	27.8	24.9
100	100 ± 15	100 ± 10	23.8	20.8
155	100 ± 18	100 ± 10	19.9	16.9
200	100 ± 20	100 ± 10	17.7	14.7
250	100 ± 20	100 ± 10	15.8	12.8
300	100 ± 20	100 ± 10	14.2	11.2
310	100 ± 20	100 ± 10	13.9	10.9
350	100 ± 22	100 ± 10	12.9	9.9

NOTES:

Notes

Jacket sequentially marked at 2 ft. intervals. US Patent #'s 5, 606, 151; 5, 734, 126; 5, 763, 823. Third party verified to TIA/EIA-568-B.2, Category 5e Patch.

PUT-UPS AND COLORS:

Item	Description	Put-Up (ft.)	Ship Weight (lbs.)	Jacket Color	Notes
1752A 0021000	4 PR #24 PP FRPVC	1000	26	RED	C

1752A Paired - Enhanced Category 5e Bonded-Pair Cables

1752A 002U1000	4 PR #24 PP FRPVC	U1000	24	RED	
1752A 0031000	4 PR #24 PP FRPVC	1000	26	ORANGE	C
1752A 003U1000	4 PR #24 PP FRPVC	U1000	24	ORANGE	
1752A 0041000	4 PR #24 PP FRPVC	1000	26	YELLOW	C
1752A 004U1000	4 PR #24 PP FRPVC	U1000	24	YELLOW	
1752A 0051000	4 PR #24 PP FRPVC	1000	26	GREEN, DARK	C
1752A 005U1000	4 PR #24 PP FRPVC	U1000	24	GREEN, DARK	
1752A 0061000	4 PR #24 PP FRPVC	1000	26	BLUE, LIGHT	C
1752A 006U1000	4 PR #24 PP FRPVC	U1000	24	BLUE, LIGHT	
1752A 0071000	4 PR #24 PP FRPVC	1000	26	VIOLET	C
1752A 007U1000	4 PR #24 PP FRPVC	U1000	24	VIOLET	
1752A 0101000	4 PR #24 PP FRPVC	1000	26	BLACK	C
1752A 010U1000	4 PR #24 PP FRPVC	U1000	24	BLACK	
1752A F2V1000	4 PR #24 PP FRPVC	1000	26	GRAY, DEC	C
1752A F2VU1000	4 PR #24 PP FRPVC	U1000	24	GRAY, DEC	

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 04-12-2006

© Copyright 2006 Belden, Inc
All Rights Reserved.

Although Belden ("Belden") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with the following environmental regulations: California Proposition 65 Consent Judgment For Wire & Cable Mfgs.(San Francisco Superior Court Nos. 312962 And 320342); EU RoHS (Directive 2002/95/EC, 27-Jan-2003);Material manufactured prior to the compliance date may still be in stock at Belden facilities and in our Distributor's inventory. EU ELV (Directive 2000/53/EC, 18-Sept-2000); EU WEEE (Directive 2002/96/EC, 27-Jan-2003); And EU BFR (Directive 2003/11/EC, 6-Feb-2003). The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information and belief at the date of its publication. The information provided in the Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.