

1864A Paired - Category 5 Unbonded-Pair Cable

 	<p>For more information please call 1-800-Belden1</p> <p><u>See Put-ups and Colors</u></p> <p>Related Documents : No. 4 for Paired Cables.pdf</p>
--	---

Description:

24 AWG solid bare copper conductors, non-plenum, Polyolefin insulation, twisted pairs, rip cord, see color code chart (below), PVC jacket (light gray or blue)

SUITABLE APPLICATIONS:

Suitable Applications	Premise Backbone Cable, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments
-----------------------	--

PHYSICAL CHARACTERISTICS:

CONDUCTOR:

Number of Pairs	25
Total Number of Conductors	50
AWG	24
Stranding	Solid
Conductor Material	BC - Bare Copper

INSULATION:

Insulation Material	PO - Polyolefin
---------------------	-----------------

Pair Color Code Chart :

Number	Color	Number	Color
1	White & Blue	14	Black & Brown
2	White & Orange	15	Black & Gray
3	White & Green	16	Yellow & Blue
4	White & Brown	17	Yellow & Orange
5	White & Gray	18	Yellow & Green
6	Red & Blue	19	Yellow & Brown
7	Red & Orange	20	Yellow & Gray
8	Red & Green	21	Purple & Blue
9	Red & Brown	22	Purple & Orange
10	Red & Gray	23	Purple & Green
11	Black & Blue	24	Purple & Brown
12	Black & Orange	25	Purple & Gray
13	Black & Green		

1864A Paired - Category 5 Unbonded-Pair Cable

OUTER SHIELD:

Outer Shield Material	Unshielded
-----------------------	------------

OUTER JACKET:

Outer Jacket Material	PVC - Polyvinyl Chloride
Outer Jacket Ripcord	Yes

OVERALL NOMINAL DIAMETER:

Overall Nominal Diameter	.526 in.
--------------------------	----------

MECHANICAL CHARACTERISTICS:

Operating Temperature Range	-30°C To +75°C
Bulk Cable Weight	135 lbs/1000 ft.
Max. Recommended Pulling Tension	100 lbs.
Min. Bend Radius (Install)	5.5 in.

APPLICABLE SPECIFICATIONS AND AGENCY COMPLIANCE:

APPLICABLE STANDARDS:

NEC/(UL) Specification	CMR, UL444
CEC/C(UL) Specification	CMR
EU CE Mark (Y/N)	Yes
EU RoHS Compliant (Y/N)	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
TIA/EIA Specification	568-B.2 Category 5
Other Specification	NEMA WC-63.1 Category 5, UL verified to Category 5

FLAME TEST:

UL Flame Test	UL1666 Riser
CSA Flame Test	FT4

PLENUM/NON-PLENUM:

Plenum (Y/N)	N
Plenum Number	1871A

ELECTRICAL CHARACTERISTICS:

Nom. Mutual Capacitance @ 1 KHz	15 pF/ft
Maximum Capacitance Unbalance (pF/100 m)	330 pF/100 m
Nominal Velocity of Propagation	71 %
Maximum Delay (ns/100 m)	538 @ 100MHz ns/100 m
Maximum Delay Skew (ns/100m)	45 ns/100 m
Maximum Conductor DC Resistance @ 20 Deg. C	9.38 Ohms/100 m
Maximum DCR Unbalance @ 20 Deg. C	5 %
Max. Operating Voltage - UL	300 V RMS

1864A Paired - Category 5 Unbonded-Pair Cable

ELECTRICAL CHARACTERISTICS - PREMISE:

Premise Cable Electricals :

Frequency (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. Structural Return Loss (dB)	Fitted Impedance (Ohms)
1	2.0		62.3	23.0	100 ± 15%
4	4.1		53.3	23.0	100 ± 15%
8	5.8		48.8	23.0	100 ± 15%
10	6.5		47.3	23.0	100 ± 15%
16	8.2		44.3	23.0	100 ± 15%
20	9.3		42.8	23.0	100 ± 15%
25	10.4		41.3	20.0	100 ± 15%
31.25	11.7		39.9	21.1	100 ± 15%
62.5	17.0		35.4	18.0	100 ± 15%
100	22.0		32.3	16.0	100 ± 15%

NOTES:

Notes	Jacket sequentially marked at 2 ft. intervals. Third party verified to TIA/EIA-568-B.2, Category 5.
-------	---

PUT-UPS AND COLORS:

Item	Description	Put-Up (ft.)	Ship Weight (lbs.)	Jacket Color	Notes
1864A 0061000	25 PR #24 PP PVC	1000	144	BLUE, LIGHT	C
1864A F2V1000	25 PR #24 PP PVC	1000	144	GRAY, DEC	C

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 07-12-2006

© Copyright 2006 Belden, Inc
All Rights Reserved.

Although Belden ("Belden") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with the following environmental regulations: California Proposition 65 Consent Judgment For Wire & Cable Mfgs. (San Francisco Superior Court Nos. 312962 And 320342); EU RoHS (Directive 2002/95/EC, 27-Jan-2003); Material manufactured prior to the compliance date may still be in stock at Belden facilities and in our Distributor's inventory. EU ELV (Directive 2000/53/EC, 18-Sept-2000); EU WEEE (Directive 2002/96/EC, 27-Jan-2003); And EU BFR (Directive 2003/11/EC, 6-Feb-2003). The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information and belief at the date of its publication. The information provided in the Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.