


Field Attachable Connector

Industrial Ethernet

RJ45 Threaded



- Create an industrial Ethernet cordset in the field using standard crimp tools
- Achieves IEC IP67 rated seal when mated with an RJ-Lnxx receptacle

When wiring a machine or premise for Ethernet connectivity, it is not always possible to know in




advance the exact length between each connection point. The RJ-Lnxx® field attachable connector enables bulk cable to be pulled to the exact required length, and then terminated to the RJ-45 plug using readily available crimp tools. The completed assembly provides the same sealed, robust connector as the RJ-Lnxx overmolded cordset.

Specifications

O-RING MATERIAL: VITON
 INSERT MATERIAL: ACRYLONITRILE-BUTADIENE-STYRENE (ABS)
 OVERMOLD MATERIAL: POLYURETHANE
 COUPLING NUT MATERIAL: ACRYLONITRILE-BUTADIENE-STYRENE (ABS)
 SHELL MATERIAL: ACRYLONITRILE-BUTADIENE-STYRENE (ABS)
 THREAD SIZE: UNC 1" - 14
 OPERATING TEMPERATURE: -20° TO 80° C
 ENVIRONMENTAL RATING: IEC IP67

CONNECTOR DIMENSIONS



PART NUMBER	DESCRIPTION
ENQAM315	FIELD ATTACHABLE RJ-45 CONNECTOR (FOR STRANDED CORE CABLE)
ENSAM315	FIELD ATTACHABLE RJ-45 CONNECTOR (FOR SOLID CORE CABLE)
EN84-2480-3040M	1000' (304M) OF SOLID CORE, CAT 5E CABLE, SHIELDED PUR (S OPTION)
EN84-2481-3040M	1000' (304M) OF PROPLEX™ STRANDED, KEVLAR WRAPPED, CAT 5 CABLE