


NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. FOR FREQUENCY RANGE FROM 10-250MHz, WITH MEASUREMENTS CALCULATED AT 250MHz, TYPICAL RESULTS ARE INDUCTANCE 9.18nH, CAPACITANCE 1.6pF.
6. ATTENUATION AND RETURN LOSS AT 22.68 MHz, THE SIGNAL FREQUENCY FOR DS3, GIVES RESULTS OF -.1 DB AND -30 DB RESPECTIVELY.
7. PART INCLUDES:
 - (1) -48 PORT PANEL WITH BNC COUPLERS ASSEMBLED
 - (1) -SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
 - (1) -SCREW KIT (INCLUDES FOUR M6 SCREWS)

MODEL FILENAME		M01156AA_ASSY_02.PRT		SIZE A
DRAWING FILENAME		M02479CF_DC59_00A.PRT		
48 PORT 75 ohm BNC PATCH PANEL CUSTOMER DRAWING				
 PANDUIT TM CORP. TINLEY PARK, ILL 60477		1.1. NUMBER N/A		
		PRODUCT SPEC N/A		
 THIRD ANGLE PROJECTION		WORK INSTRUCTION N/A		
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .031(.8) ANGLES ±		SCALE NONE		
DRAWN BY JsP		PART NO. CP48BNCBLY		
DATE 4-19-06		DRAWING NO. 02479-059		
CHK'D 				