




PANDUIT PART NUMBER*	MAXIMUM CABLE DIA. in. (mm)	WEIGHT lbs/100 pcs (g)/100 pcs	ADHESIVE BACKING
ACC38-A	0.380 (9.6)	Ⓐ 0.40 (181)	FOAM & RUBBER
ACC38-AT			FOAM & ACRYLIC

NO WARRANTY EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.



TWO UP CONFIGURATION  
(AS SUPPLIED TO CUSTOMER)

- TO APPLY ADHESIVE CORD CLIP;  
1. REMOVE MOUNT FROM PROTECTIVE LINER  
2. PLACE IN DESIRED LOCATION  
3. APPLY PRESSURE TO TOP OF  
CORD CLIP.

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

-ADHESIVE BACKING:  
ADHESIVE AND PROTECTIVE LINER.  
MOUNT IS DESIGNED TO SUPPORT 0.50lbs. (227g)  
MAX. WEIGHT ON A CLEAN DRY SMOOTH SURFACE

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS
---------------------

G00239DY\_PB\_ACC38\_01



CORP.

TINLEY PARK, ILLINOIS

ACC38-xx  
ADHESIVE CORD CLIP

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ± 0.1 (2.5) (.XXX) ± 0.020 (.5)  
(.XX) ± 0.05 (1.3) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY	MLD
----------	-----

MAT'L:	
--------	--

	SCALE
--	-------

FULL

DATE	8-8-96
------	--------

NYLON 6/6  
COLOR: NATURAL

DRAWING NO.

GB0239DY

DWG  
A  
S170

I	10-30-00	CGSM		CHANGED DIMS TO REF, REMOVED .03 DIM, CHANGED APPLICATION NOTE 1	GB0239DY	I				
R	8-8-96	MLD		INITIAL RELEASE	GB0239DY	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		