

# Product Specifications



GS8E-SL-WH

Material ID: CPC3322-08

GigaSPEED® XL GS8E Solid Low Smoke Zero Halogen Cable Modular Patch Cord, White Jacket



## CHARACTERISTICS

### Dimensions

Cord Length, maximum	100 m   300 ft
Cord Length, minimum	1 m   1 ft

### Electrical Specifications

ANSI/TIA Category	6
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	300 V

### Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)

### General Specifications

Cable Type	U/UTP (unshielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	White
Brand	GigaSPEED® XL   SYSTIMAX®
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Package, quantity	1
Pairs, quantity	4

### Mechanical Specifications

Conductor Type	Solid
----------------	-------

# Product Specifications



GS8E-SL-WH - Material ID: CPC3322-08

Material Type	Copper alloy   Polycarbonate
Outlet/Module Contact Plating	Gold over nickel
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N   30 lbf
Wiring	T568B

## Wiring Diagram

	Connector A	Connector B
Position 1	White/Orange	White/Orange
Position 2	Orange	Orange
Position 3	Lt. Green	Lt. Green
Position 4	Blue	Blue
Position 5	Lt. Blue	Lt. Blue
Position 6	Green	Green
Position 7	Lt. Brown	Lt. Brown
Position 8	Brown	Brown

## Regulatory Compliance/Certifications

### Agency

RoHS 2002/95/EC  
ISO 9001:2000

### Classification

Compliant  
Compliant



## INCLUDED PRODUCTS



### **3071E WH 4/23 RVAR** (Product Component—not orderable)

GigaSPEED® XL 3071 ETL Verified Category 6 U/UTP Cable, low smoke zero halogen, white jacket, 4 pair count, variable length, reel



### **3071E SL 4/23 RVAR** (Product Component—not orderable)

GigaSPEED® XL 3071 ETL Verified Category 6 U/UTP Cable, low smoke zero halogen, slate jacket, 4 pair count, variable length, reel

**SYSTIMAX®**  
SOLUTIONS  
www.commscope.com

©2010 CommScope, Inc. All rights reserved.  
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.  
All specifications are subject to change. See www.commscope.com for the most current information.

page 2 of 2  
10/1/2010