

Product Specifications



FFXSTST52-MX

LazrSPEED® 550 ST II to ST II Fiber Patch Cord, 3.0 mm Duplex, LSZH, Aqua Jacket

CHARACTERISTICS

Construction Materials

Fiber Type	LazrSPEED® 550, 50 µm multimode fiber
Jacket Color	Aqua
Total Fibers, quantity	2

Dimensions

Cord Length, maximum	999 ft 999 m
Cord Length, minimum	1 ft 1 m
Ordering Note	For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)

General Specifications

Construction Type	Duplex patch cord
Interface, connector A	ST
Interface Feature, connector A	Standard
Interface, connector B	ST
Interface Feature, connector B	Standard
Ordering Note	Not available in the United States or Canada

Mechanical Specifications

Cable Retention Strength, maximum	4.40 lb @ 90 ° 11.24 lb @ 0 °
-----------------------------------	----------------------------------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2000	Compliant

Product Specifications

FFXSTST52-MX



INCLUDED PRODUCTS



MFC-STU

Pre-Radiused ST II Connector, multimode
