

Product Specifications



360-iP-1100-GS3-24

Material ID: 760104984

SYSTIMAX 360™ iPatch® 1100GS3 Panel, 24 port



CHARACTERISTICS

Dimensions

Depth	40.64 mm 1.60 in
Diameter Over Dielectric, maximum	1.168 mm 0.046 in
Diameter Over Dielectric, minimum	0.762 mm 0.030 in
Height	44.45 mm 1.75 in
Weight	0.73 kg 1.60 lb
Width	482.60 mm 19.00 in

Electrical Specifications

ANSI/TIA Category	6
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel CE CSA UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Brand	iPatch® SYSTIMAX 360™ SYSTIMAX®
Product Type	Intelligent copper panel
Color	Cool gray
Package, quantity	1
Total Ports, quantity	24

Mechanical Specifications

SYSTIMAX®
SOLUTIONS
www.commscope.com

©2010 CommScope, Inc. All rights reserved.
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.
All specifications are subject to change. See www.commscope.com for the most current information.

page 1 of 2
9/29/2010

Product Specifications



360iP-1100-GS3-24 - Material ID: 760104984

Conductor Gauge, solid	22 AWG 23 AWG 24 AWG 26 AWG
Conductor Gauge, stranded	22 AWG 23 AWG 24 AWG
Material Type	ABS Polycarbonate
Outlet/Module Contact Plating	Gold over nickel
Plug Insertion Life Test Plug	IEC 60603-7 compliant plug
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N 30 lbf
Wiring	T568A T568B

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2000

Classification

Compliant
Compliant

