


Z-O12-LN-5L-F1 2BK/20G/HTS

Material ID: 760103606


Indoor/Outdoor High Tensile Strength Low Smoke Zero Halogen Single Jacket All-Dielectric Riser Rated Stranded Loose Tube Arid Core® Cable



- Additional layer of e-glass for enhanced rodent resistance

CHARACTERISTICS

Representative Image



General Specifications

Cable Type	Stranded loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled

Construction Materials

Fiber Type Solution	LazrSPEED® 300, 50 µm multimode fiber
Total Fiber Quantity	12
Fiber Type	LazrSPEED® 300, 50 µm multimode fiber
Fiber Type, quantity	12

Product Specifications

Z-012LN-5LF12BK/20G/HTS - Material ID: 760103606



Fibers Per Subunit, quantity	12
Jacket Color	Black
Jacket UV Resistance	UV stabilized

Dimensions

Buffer Tube/Subunit Diameter	2.00 mm 0.08 in
Cable Weight	114.0 lb/kft 169.0 kg/km
Diameter Over Jacket	13.10 mm 0.52 in
Filler, quantity	5
Subunit, quantity	1

Physical Specifications

Minimum Bend Radius, loaded	19.6 cm 7.7 in
Minimum Bend Radius, unloaded	13.1 cm 5.2 in
Tensile Load, long term, maximum	1334 N 300 lbf
Tensile Load, short term, maximum	1000 lbf 4448 N
Vertical Rise, maximum	807.0 m 2647.6 ft

Flame Test Specifications

Flame Test Listing	NEC OFNR-LS (ETL) and c(ETL)
Flame Test Method	IEC 60332-3 IEC 60754-2 IEC 61034-2 IEEE 383 UL-1666 UL-1685

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)

Mechanical Test Specifications

Compression	125 lb/in 22 N/mm
Compression Test Method	FOTP-41 IEC 60794-1-2, Section 7
Flex	35 cycles
Flex Test Method	IEC 60794-1-2, Section 10 FOTP-104
Impact	2.17 ft lb 2.94 N-m
Impact Test Method	FOTP-25 IEC 60794-1-2, Section 8
Strain	See long term and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1-2, Section 5
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1-2, Section 11
Water Penetration	24 h
Water Penetration Test Method	FOTP-82 IEC 60794-1-2, Section 24

Product Specifications

Z-012LN-5L-F12BK/20G/HTS - Material ID: 760103606



Environmental Test Specifications

Cable Freeze	-2 °C 28 °F
Cable Freeze Test Method	FOTP-98
Drip	70 °C 158 °F
Drip Test Method	FOTP-81 IEC 60794-1-2, Section 17
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	FOTP-28 IEC 60794-1-2, Section 28
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-104-696-2001 EN 187105 Telcordia GR-409-CORE Issue 2
-------------------------------	--

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2008

Classification

Compliant
Compliant



INCLUDED PRODUCTS



CS-5L-LT (Product Component—not orderable)
LazrSPEED® 300 OM3 Multimode Fiber