

# Product Specifications



iP-1100GS5-24

Material ID: 760051003

iPatch® GigaSPEED® X10D 1100GS5 Intelligent Patch Panel, 24 port

This product will be discontinued on: **12/31/2010**

## Replaced By:

360-iP-1100-GS5-24 SYSTIMAX 360™ iPatch® 1100GS5 Panel, 24 port



## CHARACTERISTICS

### Dimensions

Depth	38.10 mm   1.50 in
Diameter Over Dielectric, maximum	1.168 mm   0.046 in
Diameter Over Dielectric, minimum	0.762 mm   0.030 in
Height	44.45 mm   1.75 in
Weight	0.73 kg   1.60 lb
Width	482.60 mm   19.00 in

### Electrical Specifications

ANSI/TIA Category	6A
Current Rating	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm

### Environmental Specifications

Flammability Rating	UL 94 V-0
Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	Austel   CE   CSA   UL
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

**SYSTIMAX®**  
**SOLUTIONS**  
[www.commscope.com](http://www.commscope.com)

©2010 CommScope, Inc. All rights reserved.  
All trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope.  
All specifications are subject to change. See [www.commscope.com](http://www.commscope.com) for the most current information.

page 1 of 2  
9/29/2010

# Product Specifications

iP-1100GS5-24 - Material ID: 760051003



## General Specifications

Brand	GigaSPEED® X10D   iPatch®   SYSTIMAX®
Product Type	Intelligent copper panel
Color	Black
Includes	Cable management bar   Four "A" labels   Four #12 -24 mounting screws   Instruction sheet   Panel   Twenty -four cable ties
Package, quantity	1
Total Ports, quantity	24

## Mechanical Specifications

Conductor Gauge, solid	22 AWG   23 AWG   24 AWG   26 AWG
Conductor Gauge, stranded	22 AWG   23 AWG   24 AWG
Material Type	ABS   Polycarbonate
Outlet/Module Contact Plating	Gold over nickel
Plug Insertion Life Test Plug	IEC 60603-7 compliant plug
Plug Insertion Life, minimum	750 times
Plug Retention Force, minimum	133 N   30 lbf
Wiring	T568A   T568B

## Regulatory Compliance/Certifications

### Agency

RoHS 2002/95/EC

ISO 9001:2000

### Classification

Compliant

Compliant

