



Compact and Affordable 1080p HD Security Camera

- Excellent 1080p HD picture quality, supporting H.264 at 15 fps
- 3 Megapixel (2048 x 1536) maximum resolution
- Three codecs (H.264, MPEG-4, JPEG) and a dual streaming capability
- The "Exmor" CMOS sensor incorporated to realize high image quality and low noise




Key Features

Compact and stylish design for discreet surveillance solution.



- Electrical Day/Night function to switch to Day or Night mode depending on the light level.
- Stream Squared function to send two 4:3 aspect ratio videos in user-selectable resolutions up to SD simultaneously (Low-cost solution to replace two SD cameras located in a line).



• DEPA Intelligent Video Analytics system can be set up with a DEPA-enabled recorder.



- Analog monitor output (AV mini jack).
- Powered by PoE (Power over Ethernet) for simple installation.
- Recording software (RealShot Manager Lite) is bundled to start recording and monitoring instantly.
- ONVIF (Open Network Video Interface Forum) conformance that ensures greater interoperability and more flexibility in building multiple-vendor systems.




Connect Your Vision



SPECIFICATIONS

Camera	SNC-CH210
mage device	1/2.8 type progressive scan "Exmor" CMOS sensor
Minimum illumination	
	(AGC 38dB / 50IRE[IP])
Number of effective pixels	3 Megapixel
(H x V)	(2096×1561)
Electronic shutter speed	1s to 1/10000s
Gain control	Auto
Exposure control	Auto, EV Compensation, Auto Slow Shutter
White balance mode	Auto (ATW, ATW-PRO) , Preset, One-push WB, Manual
Lens type	fixed
Horizontal viewing angle	88 degrees
Focal length	f=3.3 mm
F-number	F2.8
Minimum obiects distance	500 mm
Camera Features	
Day/Night	Yes (electrical D/N)
Noise reduction	Yes
	les
Image Codec image size (H x V)	2048×1536(JpegOnly), 1920x1080, 1600x1200, 1680x1056, 1440x912, 1280x1024, 1280x960, 1376x768, 1280x800, 1280x720, 1024x768, 1024x576, 768x576, 720x576, 704x576, 800x480,
	720x480, 640x480, 640x368, 384x288, 352x288, 320x240, 320x192, 176x144
Video compression format	H.264, MPEG-4, JPEG
Codec streaming capability	Dual streaming
Maximum frame rate	H.264: 15fps (1920×1080) / 30fps (1280×720) JPEG: 12fps (2048×1536) / 15fps (1920×1080) / 30fps (1280×720) MPEG-4: 15fps (1920×1080) / 30fps (1280×720)
Scene Analytics	
Intelligent motion detection	Yes
Network	
Protocols	IPv4, IPv6, TCP, UDP, ARP, ICMP, IGMP, HTTP, HTTPS, FTP(client only), SMTP, DHCP, DNS, NTP, RTP/RTCP, RTSP, SNMP (MIB-2)
ONVIF conformance	Yes
Number of clients	5
Authentication	IEEE802.1X
Analog Video Output	
Signal system	NTSC / PAL
Interface	
Ethernet	10BASE-T / 100BASE-TX (RJ-45)
Analog monitor output	MiniJack
Sensor input	x1
General	
Mass	100g (3.5 oz)
Dimensions	ø 44 x 93 mm (1 3/4 x 3 3/4 inches)
Power requirements	PoE (IEEE802.3af compliant)
Power consumption	2.4W
Starting temperature	0°C to 50°C (32°F to 122°F)
Working temperature	0°C to 50°C (32°F to 122°F)
Storage temperature	-20°C to +60°C (-4°F to +140°F)
Safety regulation	-20 C 10 +00 C (-4 + 10 + 140 +) UL2044, FCC 158 Class A, IC Class A, IEC60950-1, EN55022(A)+EN55024+EN50130-4, VCCI Class A, C-Tick Class A
System Requirements	
Operating system	Microsoft Windows XP, Windows Vista(32bit), Windows 7(32bit)
Processor	Intel Core2 Duo 2 GHz or higher
Memory	1 GB or more
Web browser	Microsoft Internet Explorer Ver. 6.0, Ver. 7.0, Ver. 8.0 Firefox Ver.3.5 (Plug-in free viewer only) Safari Ver.4.0 (Plug-in free viewer only) Google Chrome Ver.4.0 (Plug-in free viewer only)
Supplied Accessories	
Operating system	CD-ROM (User's Guides, and supplied programs) Installation manual B&P Warranty Booklet FrontSheet(without logo) FrontSheet(without logo) Sensor input cable


SYSTEM CONFIGURATION



DIMENSIONS

Unit: mm (inches)







Distributed by

* The SNC-CH210 includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (http://www.openssl.org/).

 $\ensuremath{\textcircled{}^{\circ}}$ 2010 Sony Corporation. All rights reserved. Reproduction in whole or in part without written permission is prohibited. Features and specifications are subject to change without notice. The values for weight and dimension are approximate. Sony is a registered trademark of Sony Corporation. IPELA and "Exmor" are trademarks of Sony Corporation.

ø44 (1 3/4)

- Windows, XP, and Vista are trademarks of Microsoft Corporation.
 - Core is a trademark of Intel Corporation.

All other trademarks are the property of their respective owners.