


**THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.**




<b><i>PANDUIT</i> PART NO.</b>	<b>WEIGHT</b>
CJAST	0.9 oz. / ea. (28 g). / ea.

**NOTES:**

1. SEE CURRENT CATALOG FOR PACKAGE QUANTITY.
2. STRIPS INSULATION UP TO 0.040" (1.0mm) OF MULTI CORE CABLE, UTP/STP CABLE, FIBER OPTIC CABLE, ETC.
3. STRIP RANGE: 0.1" – 0.43" (2.5 – 11mm)
4. DIMENSIONS IN PARENTHESIS ARE IN METRIC.

[A]

										 CORP.    TINLEY PARK, ILLINOIS
										<b>CABLE JACKET ADJUSTABLE STRIPPER TOOL (CJAST) * CUSTOMER DRAWING</b>
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.x) ±    ---                    (.xxx) ±    --- (.xx) ±    .03                    ANGLES ±    ---
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
01	6-19-02	BLR	APB	REMOVE NOTE [A] AND PICTORAL	4030	---	LAH			DRAWN BY: <b>BLR</b>
00	5-16-02	BLR	APB	RELEASED	4030	---	LAH			DATE: <b>5-16-02</b>
REV	DATE	BY	CHK'D	DESCRIPTION	ECN	- R	CUST	SUP		CHK'D: <b>APB</b>
										SCALE <b>NONE</b>
										DRAWING NO. <b>CG24591B01</b>
										DWG <b>B</b> SIZE