

Product Specifications



O-006-LN-8W-F06NS


Material ID: 760002584

Single Jacket All-Dielectric Outdoor Cable Arid-Core Construction Stranded Loose Tube



CHARACTERISTICS

Representative Image



General Specifications

Cable Type	Stranded loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled

Construction Materials

Fiber Type Solution	TeraSPEED®, zero water peak single-mode fiber
Total Fiber Quantity	6
Fiber Type	TeraSPEED®, zero water peak single-mode fiber
Fiber Type, quantity	6
Fibers Per Subunit, quantity	6
Jacket Color	Black

Product Specifications

O-006LN-8W-F06NS - Material ID: 760002584



Jacket UV Resistance

UV stabilized

Dimensions

Buffer Tube/Subunit Diameter	3.00 mm 0.12 in
Cable Weight	57.0 lb/kft 85.0 kg/km
Diameter Over Jacket	11.30 mm 0.44 in
Filler, quantity	4
Subunit, quantity	1

Physical Specifications

Minimum Bend Radius, loaded	16.9 cm 6.7 in
Minimum Bend Radius, unloaded	11.3 cm 4.4 in
Tensile Load, long term, maximum	180 lbf 800 N
Tensile Load, short term, maximum	2700 N 607 lbf
Vertical Rise, maximum	958.0 m 3143.0 ft

Environmental Specifications

Environmental Space	Aerial, lashed Buried
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)

Mechanical Test Specifications

Compression	125 lb/in 22 N/mm
Compression Test Method	FOTP-41 IEC 60794-1-2, Section 7
Flex	35 cycles
Flex Test Method	IEC 60794-1-2, Section 10 FOTP-104
Impact	2.17 ft lb 2.94 N-m
Impact Test Method	FOTP-25 IEC 60794-1-2, Section 8
Strain	See long term and short term tensile loads
Strain Test Method	FOTP-33 IEC 60794-1-2, Section 5
Twist	10 cycles
Twist Test Method	FOTP-85 IEC 60794-1-2, Section 11
Water Penetration	24 h
Water Penetration Test Method	FOTP-82 IEC 60794-1-2, Section 24

Environmental Test Specifications

Cable Freeze	-2 °C 28 °F
Cable Freeze Test Method	FOTP-98
Drip	70 °C 158 °F
Drip Test Method	FOTP-81 IEC 60794-1-2, Section 17

Product Specifications

O-006LN-8W-F06NS - Material ID: 760002584



Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	FOTP-28 IEC 60794-1-2, Section 28
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards ANSI/ICEA S-87-640-2006 | EN 187105 | Telcordia GR -20-CORE Issue 3

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



INCLUDED PRODUCTS



CS-8W-LT (Product Component—not orderable)
TeraSPEED® OS2 Singlemode Fiber