







SCALE 0.500



ASSEMBLED		2	HEXAGON NUT DIN934 M4	10
PACKED IN PLASTIC BAG		1	FOAM	9.7
		4	PUSH T-wrap	9.6
		1	FLEX TUBE 350mm	9.5
		2	T-wrap	9.4
		1	WASHER STRAIN RELIEF	9.3
PACKED IN PLASTIC BAG		1	STRENGTH MEMBER CONNECTOR	9.2
		1	STRENGTH MEMBER CONNECTOR	9.1
		2	SCREW DIN7985 M3 x 5	8.4
		1	HI-D F1 PANEL BLINDPLATE	8.3
		8	OFN SADDLE	8.2
		2	CABLE MANAGEMENT SPIDER	8.1
		4	RIVET 3.2 x 6.5 - 7.5 AL	7
1933199-1		24-PORT UTP INTERFACE HOUSING KIT	6	
		HI-D F1 PANEL LOCK RIGHT	5	
		HI-D F1 PANEL LOCK LEFT	4	
		HI-D 6BLOCK FRONT F1 PANEL	3	
		HI-D F1 PANEL TRAY	2	
		HI-D F1 PANEL COVER	1	
PART NUMBER		QTY	DESCRIPTION	ITEM

CUSTOMER DRAWING		AMP port N° : 1671166	
DRAWING STATUS	REVISION DESCRIPTION	-	
RELEASED	DRAWING BY NAME: R. VANJOOREN DATE: 28-JAN-2008	DRAWING REVISION BY NAME: H. BLEUS DATE: 01-APR-2008	VOLUME (1:1 mm) 903659
SCALE: 1000	DRAWING FORMAT: A0	DRAWING TITLE	
ISO SYMBOLS	GENERAL TOLERANCE	AMP Hi-D Modular Fiber Panel	
Tyco Electronics		DRAWING SHEET REVISION NUMBER D.0017288.01.AA	REVISION AA
Tyco Electronics Belgium N.V. Diestsesteenweg 492 B-3100 HESSEL-LO, BELGIUM		THIS DRAWING AND INFORMATION SET FORTH HEREON ARE THE PROPERTY OF TYCOELECTRONICS BELGIUM N.V. AND ARE TO BE KEPT IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY TYCOELECTRONICS IS PROHIBITED.	