


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
1K	2		A	ESE0-0078-03	01SEP03	LD	JS
			B	EC ESE0-0154-04	17Nov04	LD	JS
			BI	ECR-06-004359 and Updated	17MAR2006	LD	JS
			C	ECR-06-006497	04APR2006	LD	JS

FINISHED CABLE DATA		
CONDUCTORS	WIRE AWG	24 AWG Stranded
	OVERALL DIAMETER NOM.	0.60mm (7x0.20mm)
	MATERIAL	COPPER
	PLATING	BARE
	ELONGATION	15% PER EN 50288-1
INSULATION	MATERIAL	POLYETHYLENE
	OVERALL DIAMETER	0,94
DRAIN WIRE	Ø RANGE	-
	MATERIAL	-
	PLATING	-
	ELONGATION	-
BINDER	POLYESTER TAPE	-
INDIVIDUAL PAIR SCREEN	MATERIAL	-
OVERALL SHIELD	FOIL MATERIAL	-
OVERALL SHIELD	BRAID MATERIAL	-
	PLATING	-
	COVERAGE	-
	ELONGATION	-
JACKET	MATERIAL	PVC
	OVERALL DIAMETER (D)	5,2
PULLING FORCE	MAX.	-

1. REFER TO PRODUCT SPEC 108-93018 FOR ADDITIONAL REQUIREMENTS.
2. CABLE COLORED TYPES UPON REQUEST.
3. BASENR SPECIFIC PRINT LEGEND INFO: AWG24 PRO4 CAT5e PVC UTP STRANDED.



WHITE	1000 m	REEL	1-1711060-1
WHITE	500 m	REEL	1711060-1
COLOUR	LENGTH (METRES)	PACKAGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

DWN
L. de Dios 29Aug03

CHK
A. Puell 29Aug03

APVD
J. Sanabra 29Aug03

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

tyco
Electronics

Tyco Electronics AMP España, S.A.
Barcelona. Spain.

NAME
CABLE, CAT5E, PR4,
UTP, PVC, 24AWG, STRANDED
-

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1711060

RESTRICTED TO
-

SCALE
NTS

SHEET
1

OF
1

REV
C