




CODE NO.
SEE TABLE

40.90
[1.61]

PRINTED CIRCUIT BOARD

PRINTED CIRCUIT FINGERS P1

45-78

45-78

J1

8 POSITION MODULAR JACK
2 REQUIRED

SHIELD

ADAPTER

J2

30.61
[1.205]

31.68
[1.247]

J1

1

2

3

4

5

6

7

8

PR

P1

1

2

3

4

J2

1

2

3

4

5

6

7

8

PR

SHIELD

ELECTRICAL SCHEMATIC

1

DIMENSIONS ARE MAXIMUM.

2

MATERIAL:PRINTED CIRCUIT BOARD—

LAMINATED PLASTIC SHEET,1.57 [.062] THICK.
ADAPTER—ABS MOLDING COMPOUND,SEE TABLE.
PRINTED CIRCUIT FINGERS—0.51μm [.000020] MINIMUM GOLD PLATE OVER 1.27μm [.000050] MINIMUM NICKEL PLATE.
SHIELD—BRASS WITH 5.08μm [.000200] MINIMUM BRIGHT TIN PLATE.

3.

DIMENSIONS IN BRACKETS [] ARE IN INCHES.

4.

THIS INSERT IS DESIGNED TO MATE WITH AMP INC. EDGE CONNECTOR KIT AND WALLBOX KITS.

5

THIS INTERCONNECT MEETS THE REQUIREMENTS OF IEC 603-7.

3578-1

BLACK

LIGHT ALMOND

183578-1

CODE NO

MARKINGS COLOR

ADAPTER COLOR

PART NO

CUSTOMER DRAWING FOR REFERENCE ONLY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

1

DWN
M.PANADERO
26-11-04

CHK
A.PUELL
26-11-04

APVD
J.SANABRA
26-11-04

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco

Electronics

Tyco Electronics AMP España
Barcelona, Spain.

NAME

INSERT ASSY,MOD JK,SHLD,
8 POSN,DUAL,
AMP COMMUNICATION OUTLET

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-183578

SCALE
2:1

SHEET
1 OF 1

REV
C

AMP 1470-19 REV 31MAR2000